



SPEAKER CABLE MODULAR CORD

SPEAKER CABLE

APPLICATIONS:

For use in High Definition Speaker Systems, provides a cable with low capacitance and allows it to be used with all amplifiers as opposed to other specialized high capacitance speaker wires, which cause high frequency oscillation in amplifiers.

STOCK COLOR: Clear only

* CL2 available upon request

OLYMPIC NO.	NUM. OF COND.	CONDUCTOR AWG	STRANDING	NOM. O.D.
2391	2	10	413 x 36	.240" x .485"
2392	2	12	259 x 36	.200" x .415"
2393	2	14	168 x 36	.200" x .415"
2394	2	16	105 x 36	.160" x .335"

LAMP CORD/SPEAKER CABLE

DESCRIPTION:

Stranded bare copper conductors, UL Class 11 60°C PVC, rip type construction for easy separation of conductors, one conductor ribbed for polarity i.d., surface printed with manufacturer's UL identifying code and wire gage

APPLICATIONS:

For use with fans, lamps, hanging fixtures, radios, TV sets, stereo and HiFi, small appliances and other applications

PACKAGING:

All SPT-1 and SPT-2 wires available on bulk reels (consult factory for pricing and delivery)

* Custom colors in production quantities available (consult factory for pricing and delivery)

OLYMPIC NO.	CURRENT RATING	CONDUCTOR AWG	STRANDING	UL TYPE	NOM. O.D.	AVAILABLE COLORS
2395	10 AMPS	18	41 x 34	SPT-1	.105" x .210"	BROWN, WHITE, BLACK, CLEAR
2396	10 AMPS	18	41 x 34	SPT-2	.145" x .300"	BROWN, WHITE, BLACK
2397	13 AMPS	16	65 x 34	SPT-2	.155" x .310"	BROWN, WHITE, BLACK, CLEAR
2398	4 AMPS	24	7 x 32		.050" x .120"	CLEAR

MODULAR CORD 60°C 300V

26 GAGE (7 x 34)

UL LISTED

DESCRIPTION:

Stranded bare copper, vinyl insulated, conductors parallel, silver vinyl jacket

COLOR CODE:

Four Wire - Black, Red, Green, Yellow

Six Wire - White, Black, Red, Green, Yellow, Blue

Eight Wire - Blue, Orange, Black, Red, Green, Yellow, Brown, Grey

Ten Wire - Violet, Blue, Orange, Black, Red, Green, Yellow, Brown, Grey, White

OLYMPIC NO.	NUM. OF COND.	CONDUCTOR AWG	STRANDING	NOM. O.D.
3744-26	4	26	7 x 34	.090" x .193"
3746-26	6	26	7 x 34	.090" x .280"
3748-26	8	26	7 x 34	.090" x .335"
3750-26	10	26	7 x 34	.090" x .430"

VW-1 Flame Test