



AP344244K | HC Relay Amber Type



Product name	HC Relays Amber sealed type
Product name detail	PCB, Thru-hole,24V DC
Part Number	AP344244K
Product Number	HCAE-HP-DC24V
Series	HC Relay Amber Type

※Photo may vary from actual product.

RoHS Compliant **Lead Free**

Spec Detail

As of August 28, 2012

Item	Specifications
Part Number	AP344244K
Features	Wide applications. Versatile range. Foot print compatible with competitive types.
Accessories	-
Protective construction	Sealed
Terminal shape	PCB, Thru-hole
Foreign standards	UL/CSA
Coil voltage	24
Nominal Operating Power	900mW
Pick-up voltage	19.2V DC
Drop-out voltage	2.4V DC
Nominal switching capacity (resistive load)	2A,250V AC
Min. switching capacity	1mA 1V DC
Contact arrangement	4c
Contact material	BBM
Contact material	AgNi + Au clad
Mechanical life(Min.operation)	1x10 ⁶
Electrical life	2x10 ⁵
Rated voltage (Contact-Contact)	700Vrms
Rated voltage (Contact-Coil)	2000Vrms
Ambient temperature	-40deg to +60deg
Operating function	Single side stable

© Panasonic Corporation 2012