


NICKEL CADMIUM BATTERIES: INDIVIDUAL DATA SHEET

P-500DR D size (KR33/62) Type: R

Dimensions (with tube) (mm)



Specifications

	mm	inch
Diameter	33.0 +0/-1.0	1.30 +0/-0.04
Height	61.0 +0/-1.5	2.40 +0/-0.06
Approximate Weight	Grams	Ounces
	145g	5.10

Nominal Voltage		1.2V	
Discharge Capacity*	Average**	5500mAh	
	Rated (Min.)	5000mAh	
Approx. Internal impedance at 1000Hz at charged state		5mΩ	
Charge	Standard	500mA (0.1It) x 16 hrs.	
	Rapid***	5000mA (0.33It) x 4.5 hrs.	
Ambient Temperature	Charge	Standard	°C
			°F
	Rapid		°C
			°F
	Discharge		-20°C to 65°C
			-4°F to 149°F
Storage	< 2 years		-20°C to 35°C
	< 6 months		-20°C to 45°C

* 0.2It discharge capacity after charging at 0.1It for 16 hours.

** For reference only.

*** Refer to "Charge Methods for Ni-Cd Batteries"



Battery performance and cycle life are strongly affected by how they are used. In order to maximize battery safety, please consult Panasonic when determining charge / discharge specs, warning label contents and unit design.

Note: [It] was previously expressed as [C]. [It] is an IEC standard expression for the amount of charge or discharge current and is expressed as:

$It(A) = Cn(Ah)/1h$.

- [It] is the reference test current in amperes
- [Cn] is the rated capacity of the cell or battery in Ampere-hours.
- n = the time base [hours] for which the rated capacity is declared

Typical Charge Characteristics



Typical Discharge Characteristics

