THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER*	MAXIMUM CABLE DIA. in.(mm)	WEIGHT lbs/100 pcs (g)/100 pcs	ADHESIVE BACKING
ACC38-A	0.380 (9.6)	Ⓐ 0.40 (181)	FOAM & RUBBER
ACC38-AT			FOAM & ACRYLIC

NO WARRANTY EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.



ADHESIVE BACKING:
ADHESIVE AND PROTECTIVE LINER.
MOUNT IS DESIGNED TO SUPPORT 0.50lbs.(227g)
MAX. WEIGHT ON A CLEAN DRY SMOOTH SURFACE



TWO UP CONFIGURATION
(AS SUPPLIED TO CUSTOMER)

TO APPLY ADHESIVE CORD CLIP;
1. REMOVE MOUNT FROM PROTECTIVE LINER
2. PLACE IN DESIRED LOCATION
3. APPLY PRESSURE TO TOP OF CORD CLIP.

NOTES:
1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS: G00239DY_PB_ACC38_01

PANDUIT CORP. TINLEY PARK, ILLINOIS

ACC38-xx
ADHESIVE CORD CLIP

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ±0.1(2.5) (.XXX) ± 0.020(.5)
(.XX) ±0.05(1.3) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES. THIRD ANGLE PROJECTION.

DRAWN BY: MLD
DATE: 8-8-96
CHK'D:
MAT'L: NYLON 6/6 COLOR: NATURAL
SCALE: FULL
DRAWING NO.: GB0239DY
DWG SIZE: A

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP
1	10-30-00	CGSM		CHANGED DIMS TO REF, REMOVED .03 DIM, CHANGED APPLICATION NOTE 1	GB0239DY 1		
R	8-8-96	MLD		INITIAL RELEASE	GB0239DY R		