

Products

- Products Overview
- Product Search**
- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDF-Epoxy Applic
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor
- Install & Maintain
 - Installation Instructions
 - PDF-EMA Epoxy Ad ..

Home > Products Overview > Product Search >

Current refinements (click  to remove) Search Tips 

Part Number > EMS-A-D0

Your search criteria matched only one product, shown below

EMS-A-D0



These mounts are designed for application with Panduit EMA epoxy. Especially in construction and maintenance applications where they eliminate the need to drill

- Provide a fast, strong, economical method to secure wire/cable to steel, aluminum and most other surfaces
- Eliminate the need to drill holes

Part Number	EMS-A-D0
RoHS Compliancy Status	Compliant
Part Description	Epoxy Applied Cable Tie Mount
Product Type	Cable Tie Mounts - Epoxy Applied
Material	Weather Resistant Nylon 6.6
Color	Black
Height (In.)	0.26
Height (mm)	6.6
Length (In.)	0.98
Length (mm)	24.9
Width (In.)	1.00
Width (mm)	24.9
Adhesive Type	EMA Epoxy
CE Compliant	No
Environment	Outdoor
Max. Bundle Diameter (mm)	4.8
Max. Static Load (g)	4540
Max. Static Load (Lbs.)	10.00
Mounting Method	EMA epoxy
Pricing Description	Cable Tie Mount, Epoxy Applied, WRBL
Type	Tie Mount - User Supplied Adhesive
Used With Cable Ties	M, I, S
Min. Order UOM	PC
Min. Order Qty.	500
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.