







THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT JACKETED FIBER PATCH
CORD MASTER OPTIONS LIST



1st POSITION - FIBER PRODUCT

F - FIBER

2nd POSITION - FIBER TYPE

9 - SINGLEMODE
S - SIG-CORE (OM4+)
X - OM3
Z - OM4

3rd POSITION - FIBER COUNT

2 - 2 FIBER

4th POSITION - CABLE TYPE

E - 1.6mm DUPLEX
3 - 3mm DUPLEX (SC-SC ONLY)

5th POSITION - JACKET TYPE

P - PLENUM
R - RISER
L - LSZH

6th POSITIONS - CONNECTOR (END A)

Q - PUSH PULL DUPLEX LC
L - LC DUPLEX
S - SC DUPLEX

7th POSITIONS - CONNECTOR VARIANT

1 - PUSH PULL DUPLEX LC
N - NO VARIANT

8th POSITION - CONNECTOR (END B)

Q - PUSH PULL DUPLEX LC
L - LC DUPLEX
S - SC DUPLEX

9th POSITIONS - CONNECTOR VARIANT

1 - PUSH PULL DUPLEX LC
N - NO VARIANT

10th POSITION - PERFORMANCE/POLARITY

S - STANDARD IL
T - STANDARD IL PAIR FLIPPED
O - OPTIMIZED IL
P - OPTIMIZED IL PAIR FLIPPED
N - ULTRA LOW IL (OM4 & OM4+ ONLY)

11th POSITION - PULLING EYE


N - NO PULLING EYE

12th POSITION - UNIT OF MEASURE

F - FEET
M - METERS

13th, 14th, AND 15th POSITIONS - ASSEMBLY LENGTH

F - 001-050 FEET
M - 001-050 METERS

							TITLE JACKETED DUPLEX FIBER PATCH CORDS CUSTOMER DRAWING							
							ITEM REVISION NAME M02779DX/00							
							DATASET FILE NAME M02779DX_DC/00B							
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .03 [.762] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 1 °				MATERIAL:			
							 THIRD ANGLE PROJECTION				DRAWING NUMBER: M02779DX-DC			
01	07-06-16	SAT	RWB	MMN	SEE SHEET 1 FOR REVISION HISTORY.	M02779DX-DC								
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 01-04-16	CHK RWB	SCALE NONE	SHT 2 OF 2			SIZE B

