








PANDUIT P/N	WEIGHT	SPLIT SLEEVE TYPE
NKSCM**	.10 lbs/10 pcs [45.6 g/10 pcs]	PHOSPHOR BRONZE
NKSCMZ**	.10 lbs/10 pcs [45.6 g/10 pcs]	ZIRCONIA

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR OF MODULE BASE, AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. MATERIALS:
 - a. MODULE BASE: ABS
 - b. ADAPTER HOUSING: POLYCARBONATE
 - c. SPLIT SLEEVE: PHOSPHOR BRONZE/ZIRCONIA
 - d. INNER LATCH: POLYETHERIMIDE
 - e. DUST CAP: THERMOPLASTIC ELASTOMER
4. COMPLIANT WITH TIA/EIA-604-3 (FOCIS-3) AND TIA/EIA-568-B.3
5. DIMENSIONS IN BRACKETS ARE METRIC [mm]



ISOMETRIC VIEW
SHOWN W/O DUST CAPS

										NETKEY FIBER OPTIC SIMPLEX SC ADAPTER MODULE CUSTOMER DRAWING						
											 TM CORP. TINLEY PARK, ILL 60477					
									 THIRD ANGLE PROJECTION		ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.		DRAWING FILENAME M02066AA_DC_00A.prt			
								DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (.0.3) (.XX) ± .03 (.0.B) ANGLES			SCALE NONE					
								DRAWN BY MC			REVIEW DRAWING NUMBERS		PART NO. NKSCM** / NKSCMZ**			
R	10-14-04	MC		RELEASED TO PRODUCTION	02066-05				DATE 09-20-04	SEE NOTES				DRAWING NO. 02066-05		SIZE A
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	CHK'D							

