



Search Results

- Evaluate
 - FAQ's
 - Line Cards
 - PDF-Copper Cabli ..
- Design a Solution
 - Specification Sheets
 - PDF-TX5500 Categ ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips [?](#)

Text Search: 'PFR5504OR-UY'

Your search criteria matched only one product, shown below

PFR5504OR-UY



- Exceeds requirements of ANSI/TIA-568-C.2 Category 5e and ISO 11801 2nd Edition Class D channel standards
- Exceeds requirements of ANSI/TIA-568-C.2 Category 5e and IEC 61156-5 Category 5e component standards
- Meets requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Cable diameter: 0.241 in. (6.12mm) nominal
- Installation temperature range: 32°F to 122°F (0°C to 50°C)
- Operating temperature range: -4°F to 140°F (-20°C to 60°C)
- Descending length cable markings enable easy identification of remaining cable which reduces installation time and cable scrap
- Packaged on a reel
- **Available in North America only**

• Part Number	PFR5504OR-UY
• RoHS Compliancy Status	Compliant
• Part Description	Category 5e, riser (CMR), 4-pair, F/UTP copper cable. Copper conductors are 24 AWG construction with polyethylene insulation. Conductors are twisted in pairs, surrounded by an overall polyester aluminum foil with a stranded copper drain wire and protected by a flame-retardant PVC jacket.
• Product Type	Copper Cable
• Color	Orange
• Cable Color	Orange
• Flammability Rating	CMR
• Performance Level	Category 5e/Class D
• Pricing Description	Copper Cable, Cat 5e, 4-PR, 24 AWG, F/UTP, CMR, Orange, 1000 Feet/305m
• Min. Order UOM	FT
• Min. Order Qty.	5000
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.