


"The World's Most Technically Advanced Lighting Instruments"



XENON LASER SPOT® POWER

SUBMERSIBLE TO 500 FT.

NON-INCENDIVE APPROVALS

BUILT PELI TOUGH

**PELI
PRODUCTS**

-677360 to 462-



**FULLY SUBMERSIBLE
TO 500 FT.**




**BUILT PELI TOUGH TO
PERFORM IN THE
MOST SEVERE
CONDITIONS**

TECHNICALLY ADVANCED FLASHLIGHTS & WORKLIGHTS

On land, by sea, or at 500 feet deep, Peli lights show you the way. Powerful beams and the most sophisticated lamp and reflector assemblies produce white collimated beams, or soft wide flood like beams. Peli lights offer the brightness and safety needed whether in the workplace, during recreation or at home. Used by the U.S. Military, Police and Fire Departments, and Search and Rescue Teams worldwide.

EXCLUSIVE PELI FEATURES

XENON LASER SPOT MODULAR LAMP TECHNOLOGY



DUAL FILAMENT BACK-UP SAFETY LAMPS

State-Of-The-Art dual filament lamp and circuit technology matched to a computer tuned precisely focused reflector assembly. Peli's exclusive lighting instruments are light years ahead of all imitators.


APPROVED



MSHA

CENELEC

APPROVED NON-INCENDIVE
SEE INDIVIDUAL LIGHTS FOR SPECIFIC APPROVALS



EXCLUSIVE BATTERY PROTECTION SYSTEMS

Keep fragile batteries totally safe from hard abusive dropping and life's hard knocks.


QUALITY

UNCONDITIONAL
LIFETIME
GUARANTEE
OF
EXCELLENCE

DualSix™
MANAGE SPOTLIGHT

© 1996 Peli Products

ALWAYS SOMETHING NEW AT PELI



PRIVATE LABEL PROGRAM

Peli Products offers the ultimate in private labeling. You can now put your Company name and logo or a special statement on any of Peli's flashlights or Protector Cases. Our In-house private label production department has complete short and long run capabilities for a variety of custom applications.


We have the latest state-of-the-art hot stamping equipment, utilizing the world's most durable epoxy inks and foils in our screening, hot tipping, embossing and molding programs.

All products carry Peli's legendary Unconditional Lifetime Guarantee of Excellence.

Colorful packaging from Point of Purchase displays, tube packaging, clampack and bubble cards are also available for your private label program. Our In-house graphic arts and design department is available to help create any special designs required as a Peli exclusive service.



DISTINCTIVE PACKAGING



MIGHTY POWERFUL MITYS... PACKS SMALL BEDAZZLES THEM ALL

XENON LASER SPOT™ BEAM

Produces a beam so bright and powerful it penetrates fog, water, dust and smoke.

XENON LASER SPOT® LAMP MODULE

Prefocused reflector produces a powerful collimated beam. The Xenon Laser Spot® is ideal for long range light.

LONG LIFE
ENERGIZER®
BATTERIES
INCLUDED

LIGHT BENDER FOR THOSE HARD TO SEE AND HARD TO REACH AREAS

The fibre optic design bends light beam 90° for close inspection of hard to see and get to areas.

BELT HOLSTER

Heavy duty material and stitching protects lights. 1 1/2" belt loop allows you to carry lights in a comfortable manner. Sizes to fit most lights.

NIGHT VISION LENS

Excellent for reading maps in the dark and keeping light from attracting unwanted bugs.

QUALITY

UNCONDITIONAL
LIFETIME
GUARANTEE
OF
EXCELLENCE

MityLite® Laser Spot Flashlight

SUBMERSIBLE (Batteries included)

Watertight to 500 feet. Made of an unbreakable space age high impact polycarbonate resin. Focused beam that is 400% brighter than ordinary pocket lights. INCLUDES: Shirt clip, Laser Spot lamp module, Lite Bender Accessory and 2 AAA-cell Energizer® alkaline batteries. COLORS: Black, Yellow, Orange, Blue, White, Neon Green. LENGTH: 4 3/4" DIAMETER: 5/8" CATALOG NO. 1900C

Super MityLite® LMX Laser Spot Xenon Flashlight

SUBMERSIBLE (Batteries included)

Watertight to 500 feet. 6000 candlepower. Removable shroud. Made of unbreakable "Xenon" resin. Focused beam that is 600% brighter than ordinary pocket lights. INCLUDES: Shirt clip, Lite Bender Accessory, Xenon lamp module and 2 AAA-cell Energizer® alkaline batteries. COLORS: Black, Yellow. LENGTH: 4 5/8" DIAMETER: 5/8" CATALOG NO. 1970C

SuperDuper® MityLite® 2AA

SUBMERSIBLE (Batteries included)

Watertight to 500 feet. Made of unbreakable "Xenon" resin. Focused Xenon modified spot beam is 600% brighter than ordinary personal lights. INCLUDES: Shirt clip, Xenon lamp module and 2 AA-cell Energizer® alkaline batteries. COLORS: Black, Yellow. LENGTH: 5 1/8" DIAMETER: 1 1/4" CATALOG NO. 2300C

MityLite®

SUBMERSIBLE



AUS CENELEC

Approved Non-Incendive

Super MityLite®

SUBMERSIBLE



CENELEC

Approved Non-Incendive

SuperDuper MityLite®

SUBMERSIBLE



Approvals Pending


© 1996 PELI PRODUCTS

"THE WORLD'S BRIGHTEST SWIVEL HEAD POCKET LIGHTS"



HELMET LITE HOLDER

Multi-directional adjustable light holder. Three piece set is designed to fit all Hard Hats and Fire Helmets without drilling or gluing. Attaches to either left or right side and does not interfere with visors. Fits all VersaBrite, VersaBrite II, MityLite, Super MityLite, SuperDuper MityLite and StealthLite, plus other brand lights. Molded in heat-resistant Celcon resin. COLOR: Black. WEIGHT: 2 oz. CAT. NO. 700



SPECIALY
DESIGNED FOR
HARD HATS AND
FIRE HELMETS

DESIGNED TO WITHSTAND THE MOST BRUTAL CONDITIONS

Super MityLite®/ PeliKnife™ Bonus Pack

Super MityLite® with batteries. Lock back pocket knife has 1 7/8" hollow ground stainless steel blade, lightweight composite handle, keychain ring. Presented in designer box. Folded knife LENGTH: 3" COLOR: Black. CATALOG NO. 1980



CUSTOM
IMPRINTING
AVAILABLE

KEEP HANDS FREE TO WORK

VersaBrite™

(Batteries Included)
Features Peli's 6,000 candlepower Xenon high-performance LMX lamp module. Multiple position (o-ring sealed) swivel head and made of Xenoy® resin. INCLUDES: Large multiple use visor cap/clothing clips, Nite-vision and BugsAway red lens, Velcro® mounting system, adjustable hard-hat/headband and 2 AA-cell Energizer® alkaline batteries. Burn time 5-6 hours. COLOR: Non-Glare Black. LENGTH: 3" WIDTH: 1 3/4" HEIGHT: 1 7/8" NOT FOR SCUBA APPLICATIONS. CATALOG NO. 2250C

VersaBrite II™ BIG BEAM

(Batteries Included)
Incorporates all the features of the original VersaBrite with the addition of a large 1" diameter modified spot reflector module. This produces a soft wide beam that covers 4 times the area of the collimated beam of the VersaBrite. COLOR: Non-Glare Black. LENGTH: 4 1/8" HEIGHT: 2 3/8" Swivel Head 1 1/4" NOT FOR SCUBA APPLICATIONS. CATALOG NO. 2500C



VersaBrite™

VersaBrite II™

Mini System

(Individually shrink wrapped). EACH MINI-SYSTEM INCLUDES: MityLite, spare lamp module with spring, Lite Bender, night vision red lens, spare o-ring, 2 AAA-cell Energizer alkaline batteries, and a stainless steel split ring for key-chain use. Elegantly presented in reusable designer box (available with black lid or clear lid) with a molded plush velvet liner. CATALOG NO. 1950

MULTI-PURPOSE
TRAVEL KIT

FM SP AUS GENELEC
Approved Non-Incendive

FM SP MSHA
Approved Non-Incendive

© 1996 PELI PRODUCTS

5

RUGGED, POWERFUL, BUILT PELI TOUGH



A Super PeliLite® SUBMERSIBLE TO 500 FT. The ultimate outdoor light source you can take anywhere.

The abuse proof all-purpose, outdoor spotlight that's 400% brighter and has a 400% longer lamp life. The Super PeliLite Submersible is the perfect smart looking high-tech take-along companion for all outdoor trips, leisure, or high adventure activities. Super PeliLite's weatherproof, unbreakable super bright performance makes it an instant lifetime winner for all outdoor activities. Super PeliLite's Laser Spot® Xenon lamp module has an incredible beam of light that will cut through water, smoke, fog and rain. The Super PeliLite is a perfect compact light source for industrial applications. Whether you're back-packing, whitewater rafting, or just kicking back at your favorite campsite, you can count on Super PeliLite's proven tough dependability, we guarantee it!

Super PeliLite has an unbreakable ABS body with a high impact polycarbonate lens. Requires 2 C-cell alkaline batteries (not included). COLORS: Black, Yellow, Orange. LENGTH: 6" DIAMETER: 1 5/8". CATALOG NO. 1800C.

B Super SabreLite® SUBMERSIBLE TO 2000 FT. The Industrial quality multi-purpose work horse of the professional.

Built to take a beating. The Super SabreLite, with its military tough, multi-purpose performance and quality, was selected and is used by the U.S. Army and Navy's most elite strike teams. Super SabreLite is also used by fire departments, search and rescue teams, paramedics, and literally thousands of commercial and industrial tradesmen. Super SabreLite's high-tech Xenon Laser Spot® provides four times the useable candle power of ordinary C and D size flashlights. Super SabreLite is the uncontested, no nonsense choice of the working professional. Super SabreLite is tailor made for the nastiest, potentially dangerous situations demanding the highest quality construction. You can depend on Super SabreLite's superior light transmission and guaranteed lifetime dependability. Unbreakable ABS body with a high impact polycarbonate lens.

Exclusive state-of-the-art Laser Spot® Xenon lamp module produces a tightly focused collimated white light beam with 400% increased net candle-power. INCLUDES: Belt spring clip, stainless steel split ring and black lanyard. Meets military specifications. Requires 3 C-cell alkaline batteries (not included). COLORS: Black, Yellow, Orange. LENGTH: 7 1/2" DIAMETER: 1 7/8". CATALOG NO. 2000C.

A Super PeliLite® SUBMERSIBLE




Approved Non-Incendive

B Super SabreLite® SUBMERSIBLE



Approved Non-Incendive



StealthLite®
SUBMERSIBLE

TO
500
FEET



FIM

SP

USAR

Approved
Non-Incendive

StealthLite®

Batteries Included) CATALOG No. 2400C

Watertight to 500 feet. Unbreakable ABS body with a high impact polycarbonate lens. Features Peli's state-of-the-art Laser Spot® Xenon lamp module with an unsurpassed white collimated light beam. INCLUDES: One-handed safety switch operation, double shock mounted battery compartment and black lanyard. Operates 6-8 hours on 4 AA-cell alkaline batteries (included). COLORS: Black, Yellow, Orange, Lime Green, Hot Pink. LENGTH: 6 1/2" DIAMETER: 1 5/8"


StealthLite® Clampack Packaging
(Batteries Included)

CATALOG No. 2400C.

StealthLite® Boxed

(Batteries Not Included)

CATALOG No. 2400B.



RECHARGEABLE

StealthLite®

OVER 1000 HOURS OF POWERFUL LIGHT



Peli's New Rechargeable StealthLite® offers all the features of the proven StealthLite®. It's submersible, corrosion proof and the powerful Xenon Laser Spot® beam penetrates smoke, water and fog. Used by the U.S. Armed Services, Police and Fire Departments plus Search and Rescue Teams.

The Hi-Capacity NICAD industrial battery pack yields up to 1000 charges. The burn time per charge is approximately 1 hour 10 minutes, longer if used intermittently. The rechargeable StealthLite® is 50% brighter than a standard StealthLite®.

Three long life chargers are available—12V plug-in for vehicle or boat use (Cat. No. 2456), 110 V charger (Cat. No. 2457) and a 220 V "Euro" Charger (Cat. No. 2458).

RECHARGEABLE STEALTHLITE® SYSTEM

Includes: StealthLite® Snap-In Handy Desk/Dash Mount Base; 110V Charger; High Capacity Industrial Nicad Battery Pack and High Performance Lamp. COLORS: Black, Yellow.

CATALOG No. 2450C

220V "EURO"

CHARGER

12V PLUG-IN FOR VEHICLE OR BOAT

110V CHARGER




StealthLite® RECHARGEABLE

USAR
Approved Non-Incendive



HANDY SNAP-IN BASE MOUNTS ANYWHERE
WALLS, DESKS, CANNOTS, TRUCK DASHES




HI-CAPACITY NICAD INDUSTRIAL BATTERY YIELDS UP TO 1000 CHARGES

1 HOUR 10 MINUTES BURN TIME PER CHARGE
LONGER IF USED INTERMITTENTLY

7

POWERFUL WORKLIGHTS

SUBMERSIBLE TO 500 FEET • LIGHT WHERE YOU WANT IT • HANDLE FITS LARGE GLOVED HANDS




BRITELITE™ PRO 5000 SERIES

Watertight to 500 feet. Compact 6 volt, 7 watt, 60,000 candlepower primary hand-held light source. INCLUDES: Dual Filament on back-up safety lamp with 60 hours total lamp life, shock absorbing internal battery module that protects 4 D-cells from hard use, and an integral pistol grip handle with lanyard. Choice of Laser Spot® or Modified Spot™ quick change reflectors. Made of breakable ABS housing with a high impact polycarbonate lens. Lasts 10-12 hours on 4 D-cell alkaline batteries (not included). Special buoyancy control ballast allows BriteLite to float beam for boating use or sink as desired for scuba diving. COLORS: Black, Orange, Yellow, Blue. LENGTH: 6 1/2" DIAMETER: 4 1/2". CATALOG NO. 5000B

LASER PRO™ 4D

Watertight to 500 feet. Industrial/ professional quality multi-use spotlight. Dual filament Xenon Laser Spot® safety lamp. Double switch. Burns 30 hrs. per filament (60 hrs. total). Battery burn time is 10-12 hours on 4 D-cell alkaline batteries (not included). Multi-position handle fits gloved hands. "O" ring sealed. Adjustable fold away stand. Heavy duty rubber lens protector and internal battery shock system. Floats beam up. Supplied with lanyard and equipment clip ring. COLORS: Black, Yellow. LENGTH: 6 1/2" DIAMETER: 4 1/2". CATALOG NO. 6000B



BriteLite™

LaserPro™ 4D

SUBMERSIBLE

SUBMERSIBLE




MSHA

Approved
Non-Incendive



Approved
Non-Incendive



MULTIPLE HANDLE POSITIONS

MODIFIED
SPOT™

LASER
SPOT™



KING PELI LITE™ PRO 4000 SERIES


Watertight to 500 feet. 12 volt, 14 watt, 100,000 candlepower, primary hand-held light source. Made of an unbreakable ABS housing with a high impact polycarbonate lens. INCLUDES: Dual filament Xenon safety lamp with 60 hours of lamp life (30 hours each), protective lens shroud, and a shock absorbing internal battery module that protects 8 D-cells from hard abuse. Combination pistol grip/lantern handle quickly converts to multiple positions. Choice of Laser Spot® or Modified Spot™ quick change reflectors. Operates 10-12 hours on 8 D-cell alkaline batteries (not included). COLORS: Black, Yellow, Orange, Blue. LENGTH: 9" DIAMETER: 4 1/2". CATALOG NO. 4000B

PELI DUAL SIX™ PRO 4600 SERIES


(SPECIAL PERFORMANCE SPOTLITE)

Watertight to 500 feet. Incorporates all features of #4000 King Peli Lite with the added safety of two completely separate 6 volt circuits. Each circuit consists of its own lamp filament, switch, wiring, and 4 D-cell alkaline batteries (8 D-cell batteries total). Each circuit yields 60,000 candlepower for 10-12 hours (total 20-24 hours) of continuous, uninterrupted safe lighting. Requires 8 D-cell alkaline batteries (not included). COLOR: Yellow. LENGTH: 9" DIAMETER: 4 1/2".

CATALOG
NO. 4600B



HANDY WALL MOUNT



BACK-UP LIGHT AT YOUR FINGERTIPS

ProLite™ 4C SUBMERSIBLE

Eliminate the worry and inconvenience that a burned out light or broken switch can cause. Peli's exclusive fail safe lighting system includes the dual filament XENON safety lamp and a back-up switch. The switch can also be used as an intermittent switch which automatically shuts off upon finger release. **INSTANT BACK-UP LIGHT**—The ergonomically designed switch allows you to instantly change from one filament to a second back-up filament. Quick focus adjustment for both filaments. Each filament has 30 hours of life (standard "PR" bulbs average 5 hrs.) for a total of 60 hours burn time.

NON-METALLIC/CORROSION PROOF—The ProLite™ 4C is the ideal work light for anyone preferring a non-metallic rugged light. Made of unbreakable ABS. Requires 4 C-cell alkaline batteries (not included). **COLORS:** Black, Yellow. **LENGTH:** 11" **DIAMETER:** 2 1/2" **WEIGHT:** 11 oz. **CATALOG NO. 3500B**

THE PRO'S CHOICE

400% MORE LIGHT—The ProLite™ 4C is the brightest 4 C-cell flashlight and produces 400% more light than standard 4 C-cell lights with common "PR" bulbs.



LaserFlex™ 2D

**MULTI-ANGLE FLEX HEAD
PROFESSIONAL WORKLIGHT**

Peli's LaserFlex™ 2D is designed for the working professional. Ruggedly built and just plain tough. The LaserFlex™ 2D with its powerful Xenon dual beam safety lamp performs equally well in all adverse weather conditions. Quick focus adjustment for both filaments.

The multi-angle ratchet head allows you to point the beam in any direction needed, whether hand-held or clipped on equipment, standing or laying on its side. A tough man sized tool for the abusive working conditions.

LaserFlex's ergonomically designed body allows for a secure, fatigue free grip.

**360° HEAVY DUTY
SWIVEL CLIP
ATTACHES TO
EQUIPMENT.**

**PACKS AND
TURN OUT
COATS**



LaserFlex™ 2D Is the industrial quality multiple angle flex head ergonomically designed personal spotlight. Incorporates sealed Xenon Laser Spot™ double filament safety lamp. Operates 30 hours on each independent filament. Standard PR based bulbs average 5 hrs. Double switched for additional backup safety. Battery burn time 8-10 hrs. on 2 D-cell alkaline batteries (not included). Separate intermittent blinker switch in addition to double main switch. Water resistant only. Heavy duty lanyard and equipment clip ring included. Non-incendive approvals pending. **COLORS:** Black, Yellow. **LENGTH:** 8-1/2" **DIAMETER:** (at head): 2 3/4". **CATALOG NO. 3000B**
NOT FOR SCUBA APPLICATIONS