

Wall mounted cases - CONCEPTLINE

Wall mounted case



41102002


- Type of protection IP 66
- With gland plate
- Door opening angle 130°

Delivery comprises (assembled)

Item	Qty	Description
1	1	Basic case, St, 1.5 mm, RAL 7035
2	1	Door, St, 1.5 mm, RAL 7035, with gasket
3	1	Gland plate, supplied loose, St, 1.5 mm (800 mm wide cases have 2 gland plates)
4	1 / 2	Lock, 3 mm double bit, case height up to 500 mm, 1 lock, case height over 600 mm, 2 locks
5	1	Assembly kit

Order Information

Case Height H	Width W	Depth D	Weight kg	Gland plate		Part no.
				Width w	Depth d	
300	250	150	5.3	187	62	12506-004
300	300	220	7.4	220	100	12506-010
400	300	150	7.6	187	62	12506-005
400	300	220	9.0	220	100	12506-011
400	400	220	10.5	220	100	12506-012
400	600	220	13.9	220	100	12506-017
500	400	220	13.0	220	100	12506-013
500	500	220	14.4	420	100	12506-015
500	500	320	17.9	420	100	12506-030
600	500	150	15.2	318	62	12506-003
600	400	220	14.9	220	100	12506-014
600	600	220	20.5	420	100	12506-018
600	600	320	24.0	420	100	12506-031
800	600	220	25.4	420	100	12506-019
800	800	220	32.0	220	100 1)	12506-020
800	600	320	29.4	420	100	12506-032
800	600	420	31.4	420	100	12506-054
1000	600	220	31.0	420	100	12506-022
1000	600	320	34.0	420	100	12506-041
1200	600	320	40.0	420	100	12506-033
1200	600	420	44.0	420	100	12506-055



const002

Wall mounting bracket St, 2.5 mm, zinc-plated, PU 4 pieces

CMFK

T-bar lock with 2 keys, PU 1 kit

62406-096


GND/earthing, 2 x Cu wire, green/yellow, PU 1 kit

12406-400


1) with 2 gland plates 220 mm x 100 mm

Note

- Smaller cases in chapter INLINE; further versions available on request



Wall mounting bracket



T-bar lock

const021 41105050



For further information www.schroff.biz/oneclick
oneClick search code = Part no.



ServicePLUS see page 2.46