



24 Watt Universal Input Medical Adapter Series PSS-22U Switching Power Supplies Series



Features

- Universal Input
- Medical Approval
- EMI Class B

Applications

- Blood Analyzer
- Non-Patient Connect Instruments

Safety Approvals

- cUL 2601 Class I
- CE
- Nemko EN60601 (IEC601)

Mechanical Characteristics

- Dimensions:
- Length: 110mm (4.33in)
 - Width: 58mm (2.28in)
 - Height: 32.3mm (1.27in)
 - Weight: 206gm (6.23oz)

Output Specifications

Model	DC Output Voltage	Output Current	Ripple P-P	Regulation	
				Line	Load
PSS-22U-033	3.3V	4.00A	±1%	0.1%	±3.0%
PSS-22U-050	5.0V	4.00A	±1%	0.1%	±3.0%
PSS-22U-120	12.0V	2.00A	±1%	0.1%	±3.0%
PSS-22U-150	15.0V	1.60A	±1%	0.1%	±3.0%
PSS-22U-240	24.0V	1.00A	±1%	0.1%	±3.0%

(1) All measurements are at normal input, full load, and +25° C.

(2) Load regulation is measured at 115VAC or 230VAC in percentage to indicate the change in output voltage as the load varied from half load to full load(±%)

INPUT:**AC Input Voltage**

90 to 264 VAC

AC Input Frequency

47 to 63Hz

AC Input Current

0.6A @ 115VAC

0.3A @ 230VAC

AC Inrush Current

15A @ 110VAC

30A @ 230VAC

EMI (Conducted)

EN 55022 FCC Class B

AC Leakage Current

Less than 0.1 mA @ 264VAC

OUTPUT:**Hold-up Time**

16mS @ 115VAC

64mS @ 230VAC

Overload Protection115-130% of max. power of
overrange or short circuit, power
foldback & self-recovering**GENERAL:****Efficiency**

Typical 80%

Operation Temperature

0 to +40°C

Storage Temperature

-20°C to +85°C


Transient ResponseOutput Voltage Returns in Less
than 3mS Following a 50% Load
Change**Construction**Impact Resistant Thermo-Plastic
Enclosure Case SE100 94VO Nylon**Dielectric Withstand**

1612V rms: Primary to Ground

4000V rms: Primary to Secondary

DC Output Connector

Center Positive Standard

Dimension Diagram Unit: mm (inch)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phihong:

[PSS-22U-050](#) [PSS-22U-240-LF](#) [PSS-22U-120](#) [PSS-22U-150](#) [PSS-22U-033](#) [PSS-22U-150-LF](#) [PSS-22U-120-LF](#)