

Farnell Module Maintenance

Module: **450602** Width: **85.00mm** Operator: **SHORTRG** Print date & time: **13 Dec 2011 ● 10:05**

ExternalRefs:	MAMRefs:
ModuleRefs:	TreeNodeRefs:
ProdRefs: 42539498, 42539499, 42539500	Primary ProdRefs: <i>42539498, 42539499, 42539500</i>
SecondaryProdRefs: 42539498, 42539499, 42539500	SecProdRefsbymodname: <i>FIO Philips - Infra-Red Heat Lamps #F</i>

Division: **Master Modules** IndexType: **Descriptive Index**
Publication: **PRODUCT PORTFOLIO** Primary word: **Infrared**
Book: **ELECTRICAL** Secondary Word: **Lamps**
Section: **Lamps**
Product Group: **Farnell InOne**
Product SubGroup: **GLS Filament Lamps**
Module: **FIO Philips - Infra-Red Heat Lamps #F**

Infra-Red Heat Lamps

PHILIPS



Hard Blown (R125)



Hard Pressed (PAR38)

- Infra-red tungsten filament heat lamps in both R125 and PAR38 styles
- 5000 hours average life
- **Hard Blown** version (R125) resisitant to thermal shocks, such as water splashes, making it suitable for industrial applications
- **Hard Pressed** versions have a high-efficiency reflector and refractor lens design, allowing accurate heat direction to where it is needed
- ES fitting
- Voltage: 240V / /250V

450602

Type	Watts	Mfrs. List No.	Order Code	1 +	10 +	50 +
Hard Blown	250W	12649825	130-3431 ●	13.39	12.17	11.13
Hard Pressed	100W	12893520	130-3432 ●	7.69	7.00	6.50
Hard Pressed	175W	12895920	130-3433 ●	13.01	11.86	10.92