




Philips
Magic 5 Primo
Plain paper fax
+ telephone and copier

Primo



PPF 631



fax it, say it

with Philips Magic 5 Primo

The Magic 5 series offers you the usual reliability of Philips plain paper faxes. Moreover it comes in a new and innovative design and is smaller than ever. Distinctive ringtones, predefined fax forms and outgoing call log are only a few of this machine's various features that will make your life easier and more comfortable.

Reliable plain paper fax

Stores up to 15 pages

Feature-rich telephone

Allows distinctive ringtones

Easy to use copier

With fine-/photo resolution

PHILIPS

Product Specifications

Main features

Ink-film fax

- ITU Group 3 compatible (T.30 standard/T.30 new)
- 9.600 bps modem speed, auto fall back
- Horizontal resolution: 8 pixels/mm
vertical resolution standard: 3.85 lines/mm
vertical resolution fine: 7.7 lines/mm
- Page header, automatic redial
- Sending report with reduced copy of the first page
- Printing method: thermal transfer
- 10 page automatic document feeder (ADF)
- Predefined fax forms
- Sudoku printing with solutions (easy - medium - tough - devil)
- Timer function (send later)
- Up to 15 page memory
- Group broadcasting
- Easy polling (receive and send)
- Paper tray up to 50 sheets
- Cordless phone management

Telephone

- 50 name dial entries
- 10 ringer melodies
- Caller identification (CLIP)*
- Distinctive ring tones**
- 10 short dial keys
- On hook dialling
- Chain dialling
- Redial of the last 10 numbers
- Outgoing call log print

Copier

- Multicopy up to 15 pages
- Fine-/photo-resolution
- Zoom-function (enlarge/reduce)
- 16 grey scales

* Depends on the availability of the service on the local operators network

** Depends on the availability of caller identification

General information

Power consumption

- | | |
|--------------------------|------------|
| · Stand by | typ. 1,5 W |
| · Transmission | typ. 15W |
| · Reception | typ. 15W |
| · Copy | typ. 15W |
| · Telephone conversation | typ. 4W |

Display

- Liquid crystal-display (LCD), 16 characters/
1 line, European characters

Installation

- Easy-install menu and help pages

Dimension (WxDxH)

- | | |
|------------|---------------|
| · Unpacked | 313x197x129mm |
| · Packed | 377x247x200mm |

Weight

- | | |
|----------------------------------|-------|
| · Unpacked (without accessories) | 2,4kg |
| · Packed (incl. country kit) | 3,3kg |

Temperature range

- | | |
|--------------------|----------------|
| · Operation | 5° C - 40° C |
| · Storage packed | -25° C - 50° C |
| · Storage unpacked | 0° C - 45° C |

Relative humidity

- | | |
|--------------------|-----------|
| · Operation | 15 - 85 % |
| · Storage packed | 5 - 95 % |
| · Storage unpacked | 15 - 85 % |

Standard package includes

- Fax machine incl. cables (mains and telephone network)
- Starter ink film
- User-manual including installation-guide

Accessories

- Philips PFA 351 with PLUG'N'PRINT Card/up to 140 pages A4

9 NC

Type number

288090XXX

EAN code

PPF 631/XXB

Designed for

342516017XXXX

Power supply

PSTN/PABX

195 - 264V AC/ 47 - 63Hz



www.fax.philips.com

© 2006 SAGEM Communication Austria GmbH.
All rights reserved. The information and specifications included are subject to change without prior notice. SAGEM tries to ensure that all information in this document is correct, but does not accept liability for error or omission.