

HC-B 16-TFQ-N-O1STM25G

Order No.: 1460128



<http://catalog.phoenixcontact.net/phoenix/treeViewClick.do?UID=1460128>

HEAVYCON B16 sleeve housing, for double locking latch, height: 65 mm, with 1 x M25 thread, straight cable outlet

Commercial data

EAN	
sales group	D002
Pack	10 Pcs.
Customs tariff	85389099
Gross weight in pieces	KG
Net weight per piece	KG
Catalog page information	Page 514 (CAT-4-2013)

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Note	For contact inserts HC-B16, BB32, D40, DD72, HS6, M, K
Design	B16
Height	65 mm
Width	43 mm
Length	94 mm
Housing type	Sleeve housings
Locking type	For double locking latch

No. of cable exits	1
Cable exit	Straight
Screw connection	None
Type of the screw connection	1x M25
Degree of protection for housing	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray

Certificates / Approvals


Certification

Certifications applied for:

Certification Ex:

Drawings

Dimensioned drawing



Dimensional drawing

Address

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 00
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>



© 2012 Phoenix Contact
Technical modifications reserved;