

Fiber optic cables - VS-P1215-P1218-C1001/ 2,0 - 1608980

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid
(<http://download.phoenixcontact.com>)



Assembled PROFINET-fiber optic cable, round cable, HCS fiber 200/230 µm, SCRJ/IP67 push-pull plastic housing on SCRJ/IP20, for installation inside buildings, length: 2 m



Key commercial data

Packing unit	1 PCE
GTIN	 4 046356 161480
Custom tariff number	85447000
Country of origin	GERMANY

Technical data

Mechanical characteristics

Number of positions	2
Connection profile	SCRJ in acc. with IEC 61754-24
Locking type	Push Pull
Fiber	200/230 µm
Number of fibers	2.00
Insertion/withdrawal cycles	≥ 500
Cable diameter	7.50 mm
Type of cable	Round cable
Length of cable	2 m
Ambient temperature (operation)	-20 °C ... 70 °C (cable, fixed installation)
Ambient temperature (operation)	-10 °C ... 60 °C (cable, flexible installation)
Ambient temperature (operation)	(Plug / socket)

Material data

Housing material	PA-GF/PBT
------------------	-----------

Fiber optic cables - VS-P1215-P1218-C1001/ 2,0 - 1608980

Technical data

Material data

Material, O-ring	NBR
Cable seal material	TPE
Outer sheath, material	LSFH
External sheath, color	green-yellow RAL 6018
Ferrule holder color	Red
Degree of protection	IP67/IP20

Optical characteristics

Attenuation	≤ 1.2 dB (With 850 nm)
-------------	------------------------

Classifications

ETIM

ETIM 3.0	EC000034
ETIM 4.0	EC001476
ETIM 5.0	EC000034

UNSPSC

UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501


eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27061803
eCl@ss 6.0	27061090
eCl@ss 7.0	27061090

Drawings


Fiber optic cables - VS-P1215-P1218-C1001/ 2,0 - 1608980

Schematic diagram




Pin assignment plug SCRJ

Dimensioned drawing




SCRJ Push-Pull connector, IP67

Schematic diagram



Pin assignment plug SCRJ

Dimensioned drawing



SCRJ connector IP20