

Housing - HC-HV 3-AMQ - 1773585

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

HEAVYCON panel mounting base HV3, with double locking latch, height 27 mm



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 037772
Weight per Piece (excluding packing)	148.8 GRM
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	27 mm
Width	43 mm
Length	93 mm
Length of the assembly cutout	64 mm
Width of the assembly cutout	35 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HV-HV3
Design	HV3
Housing type	Panel mounting base
Locking type	With double locking latch
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray

Housing - HC-HV 3-AMQ - 1773585

Technical data

General

Material lock	Stainless steel, handle: PA
Material grip body interlock	PA

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

GOST

Ex Approvals

Housing - HC-HV 3-AMQ - 1773585

Approvals

Approvals submitted

Approval details

GOST 