

SFLY 2,5/F32/ZD

Order No.: 2285470

The illustration shows the version SFLY 2,5/F 32/ZB



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2285470>

Screw socket, Nominal current: 4 A, Number of positions: 32, Pitch:
5.08 mm, Color: green

Commercial data

GTIN (EAN)	 4 017918 055950
sales group	E311
Pack	10 pcs.
Customs tariff	85369010
Catalog page information	Page 344 (CC-2005)

Product notes

WEEE/RoHS-compliant since:
05/27/2008



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

Dimensions / positions

Length	40 mm
Height	35.5 mm
Width	95 mm
Pitch	5.08 mm
Number of positions	32

Hole diameter	2.8 mm
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

Technical data

Range of articles	SFLY 2,5
Insulating material group	I
Rated surge voltage (III/3)	4 kV
Connection in acc. with standard	EN-VDE
Nominal current I_N	4 A
Nominal voltage U_N	250 V
Insulating material	PA
Inflammability class acc. to UL 94	V2
Stripping length	8 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Certificates / Approvals




Certification

GOST

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;