

FLKM 14-PA-MODI-A120

Order No.: 2289450



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2289450>

VARIOFACE front adapter, for Schneider Electric MODICON TSX-Compact (A120, 984), 2 x 8 channels can be connected

Commercial data

EAN	4017918057572
Pack	5 pcs.
Customs tariff	85369010
Weight/Piece	0.03885 KG
Catalog page information	Page 154 (IF-2002)

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Channels which can be connected	16
Connection type, plug connector	Flat-ribbon cable plug connector in acc. with IEC 60603-13
Number of plug connectors	2
No. of positions, plug connector	14
Number of positions	14
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Mounting position	Any
Standards/regulations	IEC 60664
	IEC 60664 A
	DIN VDE 0110
	DIN VDE 0160 (in parts)
Max. permissible current	1 A (per path)
Max. permissible total current	3 A (Per Byte, for supply via connector)
Pollution degree	2
Surge voltage category	II
Supported controller	Schneider Electric MODICON A 120

Supported I/O card	DEO 216
	DEP 214
	DEP 215
	DEP 216
	DEP 217
	DEP 296
	DEP 297
	DAO 216
	DAP 216
	ADU 204
	ADU 205
	ADU 206
	ADU 210
	DEP 220
	ADU 214
	DAU 202
	DAU 208

Certificates / Approvals




Certification

CUL, GOST, UL

Diagrams/Drawings

Circuit diagram



Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;