

CD 40X60

Order No.: 3240192



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=3240192>

Wiring channel, gray, consisting of upper and lower part, width: 40 mm, height: 60 mm, length 2000 mm

Commercial data

GTIN (EAN)	 4 046356 459150
sales group	B204
Pack	20 pcs.
Customs tariff	39259020
Catalog page information	Page 102 (NTK-2010)

Product notes

WEEE/RoHS-compliant since:
10/08/2008



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Length (b)	2000 mm
Height	60 mm
Width (a)	40 mm
Color	gray
Inflammability class acc. to UL 94	V0

Ambient temperature (operation)	-5 °C ... 60 °C
Material	PVC

Certificates / Approvals

Certification

CSA, UL, VDE-PZI

Accessories

Item	Designation	Description
General		
3240286	CD COVER 40	Cover for cable duct, gray, width: 40 mm, length: 2000 mm
3240284	CD WR	Universal wire holding bracket, perforated, for wiring channels
3240498	RVT-PA 4	Plastic body-bound rivet, 4 mm diameter, for a material thickness of 1.5 ... 6 mm
3240499	RVT-PA 6	Plastic body-bound rivet, 6 mm diameter, for a material thickness of 1.5 ... 6 mm
1212478	UNIFOX-RVT P 4	Rivet setting tool, for use with RVT-PA 4 plastic body-bound rivets
1212509	UNIFOX-RVT P 6	Rivet setting tool, for use with RVT-PA 6 plastic body-bound rivets

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;