

## TCP 1A

Order No.: 0712194

The illustration shows version TCP 2A



Thermal miniature circuit breaker, pluggable in screw-type fuse terminal block UK 6-FSI/C and spring-cage fuse terminal block ST 4-FSI/C

Commercial data	
EAN	4017918848354
Pack	20 Pcs.
Customs tariff	85362010
Weight/Piece	0.010941 KG
Catalog page information	Page 390 (CL-2007)

### Product notes

WEEE/RoHS-compliant since:  
01/01/2003



Technical data	
<b>General</b>	
Color	black
Insulating material	PA
Inflammability class acc. to UL 94	V0

**Dimensions**

Width	8.2 mm
Length	24.5 mm
Height NS 35/7,5	55 mm

**Technical data**

Fuse	Slow-blow
Fuse type	Automatic device
Nominal current $I_N$	1 A
Nominal voltage $U_N$	250 V AC 65 V DC
Switching capacity $I_{CN}$	(6x $I_N$ for nominal currents 0.25 A to 4 A) (8x $I_N$ for nominal currents 6 A to 10 A)
Ambient temperature (operation)	-20 °C ... 60 °C

**Certificates / Approvals**



Certification

CUL, GOST, UL, VDE-PZI

**Accessories**

Item	Designation	Description
------	-------------	-------------

**Marking**

0807180	ZBFM 5/OG:UNBEDRUCKT	Zack marker sheet, flat, unprinted: 120-section, 10 strips à 12 markers, sufficient for 120 terminal blocks, for all terminal blocks, pitch 5.2 mm, labeling with M-PEN or CMS system, color: orange
0803595	ZBFM 5/WH:UNBEDRUCKT	Zack marker sheet, flat, unprinted: 120-section, 10 strips à 12 markers, sufficient for 120 terminal blocks, for all terminal blocks, pitch 5.2 mm, labeling with M-PEN or CMS system, color: white
0803647	ZBFM 5:SO/CMS	Special printing, Zack marker sheet, flat, 120-section, divisible, marking according to customer requirements

Dimensioned drawing

