




Model 3690 "X" = (11,43mm) 0.45"
"L" = (22,61mm) 0.89"
Model 4617 "X" = (25,40mm) 1.00"
"L" = (36,32mm) 1.43"

FEATURES:

- Supports 20 to 22 AWG wires.
- Allows creation of custom patch cord lengths.
- Insulator unthreads to allow easy Do-It-Yourself wire soldering.
- Banana plug body & spring are gold plated for corrosion resistance and optimum electrical connection between plug and jack.
- Banana plug spring is Beryllium Copper for superior spring shape retention to ensure long insertion life.

MATERIALS:

Insulator Cap: Nylon, Color per part number

Miniature Banana Plug: Body – Brass, Gold Plated

Spring – Beryllium Copper, Gold Plated

RATINGS:

Operating Voltage: 2500 VDC

Operating Temperature: +80°C (+176°F)

Current: 5 Amperes Max.

ORDERING INFORMATION: Models 3690-* & 4617-*

* = Color, -0 Black, -2 Red

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90324 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com