


Patch Cords

Stacking Banana Plug



Brass body, beryllium copper spring. **Insulation:** Polypropylene. **Wire:** 18 AWG, 65 x 36 t.c., PVC insulated, 3.66 mm (.144) O.D. **Rating:** 5000 VDC; 15 amps, +55°C (+131°F) max.

885-0025	B-4-0	Black, 4"	EACH	3.70
885-0026	B-4-2	Red, 4"	EACH	3.70
885-0027	B-8-0	Black, 8"	EACH	3.70
885-0028	B-8-2	Red, 8"	EACH	3.70
885-0014	B-12-0	Black, 12"	EACH	3.70
885-0019	B-12-2	Red, 12"	EACH	3.70
885-0015	B-18-0	Black, 18"	EACH	3.70
885-0020	B-18-2	Red, 18"	EACH	3.70
885-0016	B-24-0	Black, 24"	EACH	3.70
885-0022	B-24-2	Red, 24"	EACH	3.70
885-0017	B-36-0	Black, 36"	EACH	3.70
885-0029	B-36-2	Red, 36"	EACH	3.70
885-0018	B-48-0	Black, 48"	EACH	4.10
885-0030	B-48-2	Red, 48"	EACH	4.10
885-4004	B-60-0	Black, 60"	EACH	4.10
885-4005	B-60-2	Red, 60"	EACH	4.10
885-4006	B-72-0	Black, 72"	EACH	4.10
885-4007	B-72-2	Red, 72"	EACH	4.10

Miniature Stacking Banana Plug Each End



1st End: Stacking miniature banana plug. Brass body, beryllium copper spring, gold plated. **Insulation:** Polypropylene. **Wire:** 20 AWG, 41 x 36 t.c., PVC insulated, 2.2 (.087) O.D. **2nd End:** Stacking miniature banana plug. Brass body, beryllium copper spring, gold plated. **Insulation:** Polypropylene. **Rating:** 3000 VDC, 5 amps, +55°C (+131°F) max.

885-1084	1081-12-0	Black, 12"	EACH	5.05
885-1085	1081-12-2	Red, 12"	EACH	5.05
885-1086	1081-18-0	Black, 18"	EACH	5.05
885-1087	1081-18-2	Red, 18"	EACH	5.05
885-1088	1081-24-0	Black, 24"	EACH	5.05
885-1089	1081-24-2	Red, 24"	EACH	5.05
885-1090	1081-36-0	Black, 36"	EACH	5.05
885-1091	1081-36-2	Red, 36"	EACH	5.05
885-1092	1081-48-0	Black, 48"	EACH	5.40
885-1093	1081-48-2	Red, 48"	EACH	5.40
885-1094	1081-60-0	Black, 60"	EACH	5.40
885-1095	1081-60-2	Red, 60"	EACH	5.40

Minigrabber® Test Clip to Stacking Banana Plug



1st End: Minigrabber®. **Contact:** Beryllium copper, gold plated. **Insulation:** Glass filled nylon. **Wire:** 20 AWG, 41 x 36 t.c., PVC insulated, 2.21 mm (.087) O.D. **2nd End:** Stacking banana plug. Brass body, beryllium copper spring, nickel plated. **Insulation:** Polypropylene. **Rating:** 300 VAC, 5 amps, +55°C (+131°F) max.

885-0920	3782-12-0	Black, 12"	EACH	3.40
885-0921	3782-12-2	Red, 12"	EACH	3.40
885-0922	3782-24-0	Black, 24"	EACH	3.40
885-0923	3782-24-2	Red, 24"	EACH	3.40
885-5446	3782-36-0	Black, 36"	EACH	3.40
885-5447	3782-36-2	Red, 36"	EACH	3.40
885-0924	3782-48-0	Black, 48"	EACH	3.70
885-0925	3782-48-2	Red, 48"	EACH	3.70
885-0926	3782-60-0	Black, 60"	EACH	3.70
885-0927	3782-60-2	Red, 60"	EACH	3.70

Minigrabber® Test Clips to Stacking Banana Plug on Coiled Cord

20 AWG wire, PVC insulated, 48" ±1" extended length. **Rating:** 300 VAC continuous duty, 5 amps, +55°C.

885-4536	4538-0	Black	EACH	9.90
885-4539	4538-2	Red	EACH	9.90

Minigrabber® Test Clip to Minigator



1st End: Minigrabber®. **Contact:** Beryllium copper, gold plated. **Insulation:** Glass filled nylon. **Wire:** 20 AWG, 41 x 36 t.c., PVC insulated, 2.21 mm (.087) O.D. **2nd End:** Minigator. Steel, nickel plated. **Insulation:** Vinyl. **Rating:** 45 VAC, 5 amps, +50°C (+122°F) max.

885-0953	4652-12-0	Black, 12"	EACH	5.40
885-0954	4652-12-2	Red, 12"	EACH	5.40
885-0955	4652-24-0	Black, 24"	EACH	5.40
885-0956	4652-24-2	Red, 24"	EACH	5.40

Minigrabber® Test Clip One End Only



Wire: 20 AWG, 41 x 36 t.c., PVC insulated, 2.21 mm (.087) O.D. **Rating:** 300 VAC, 12 amps.

885-0986	3780-60-0	Black, 60"	EACH	2.65
885-0987	3780-60-2	Red, 60"	EACH	2.65

Minigrabber® Test Clip Each End



Wire: 20 AWG, 41 x t.c. PVC insulated, 2.21 mm (.087) O.D. **Rating:** 300 VAC, 12 amps.

885-5432	3781-8-0	Black, 8"	EACH	3.40
885-5433	3781-8-2	Red, 8"	EACH	3.40
885-0910	3781-12-0	Black, 12"	EACH	3.40
885-0911	3781-12-2	Red, 12"	EACH	3.40
885-0916	3781-18-0	Black, 18"	EACH	3.40
885-0917	3781-18-2	Red, 18"	EACH	3.40
885-0912	3781-24-0	Black, 24"	EACH	3.40
885-0913	3781-24-2	Red, 24"	EACH	3.40
885-5438	3781-36-0	Black, 36"	EACH	3.40
885-5439	3781-36-2	Red, 36"	EACH	3.40
885-0914	3781-48-0	Black, 48"	EACH	3.70
885-0915	3781-48-2	Red, 48"	EACH	3.70
885-0918	3781-60-0	Black, 60"	EACH	3.70
885-0919	3781-60-2	Red, 60"	EACH	3.70

Minigrabber® Test Clip Patch Cord Kit

Kit contains 10 pieces of model 3781-24. One of each color.


885-6027	5523	EACH	30.15
----------	------	------	-------

Micrograbber® Test Clip to Stacking Banana Plug

20 AWG PVC insulated wire. **Rating:** 150 VAC, 3 amps, +55°C.

885-5053	5053-12-0	Black, 12"	EACH	5.35
885-5054	5053-12-2	Red, 12"	EACH	5.35
885-5055	5053-24-0	Black, 24"	EACH	5.35
885-5057	5053-24-2	Red, 24"	EACH	5.35
885-5058	5053-36-0	Black, 36"	EACH	5.35
885-5059	5053-36-2	Red, 36"	EACH	5.35
885-5060	5053-48-0	Black, 48"	EACH	5.65
885-5061	5053-48-2	Red, 48"	EACH	5.65

Micrograbber® Each End



1st End: Micrograbber®. **Contact:** Beryllium copper, gold plated. **Insulation:** Glass filled nylon. **Wire:** 20 AWG, 41 x 36 t.c., PVC insulated, 2.21 mm (.087) O.D. **2nd End:** Same as first end. **Rating:** 150 VAC, 3 amps, +102°C (+216°F) max.

885-4613	4613-12-0	Black, 12"	EACH	5.45
885-4614	4613-12-2	Red, 12"	EACH	5.45
885-4615	4613-24-0	Black, 24"	EACH	5.45
885-4616	4613-24-2	Red, 24"	EACH	5.45
885-4617	4613-36-0	Black, 36"	EACH	5.45
885-4618	4613-36-2	Red, 36"	EACH	5.45
885-4619	4613-48-0	Black, 48"	EACH	5.45
885-4620	4613-48-2	Red, 48"	EACH	5.45

Micrograbber® Test Clip Patch Cord Kit

Kit contains 10 pieces of model 4613-24. One each of ten colors.

885-6026	5525	EACH	49.00
----------	------	------	-------

Insulated Alligator Clip Each End



18 AWG. **Rating:** 150 VAC, 5 amps, +50°C.


885-0060	AL-B-12-0	Black, 12"	EACH	4.10
885-0061	AL-B-12-2	Red, 12"	EACH	4.10
885-0062	AL-B-24-0	Black, 24"	EACH	4.10
885-0063	AL-B-24-2	Red, 24"	EACH	4.10
885-0064	AL-B-36-0	Black, 36"	EACH	4.10
885-0065	AL-B-36-2	Red, 36"	EACH	4.10

Insulated Alligator Clip Kit

885-3907, 6356-36. Kit of 10 different colors, 36"

885-3907	6356-36	Kit of 10 different colors, 36"	EACH	39.00
----------	---------	---------------------------------	------	-------

Stacking Pin Tip Plug



Brass body, beryllium copper spring, gold plated. **Insulation:** Polypropylene. **Wire:** 20 AWG, 41 x 36 t.c., PVC insulated, 2.21 mm (.087) O.D. **Rating:** 3000 WVDC; 5 amps, +55°C (+131°F) max.


885-0050	P-4-0	Black, 4"	EACH	4.45
885-0051	P-4-2	Red, 4"	EACH	4.45
885-0052	P-8-0	Black, 8"	EACH	4.45
885-0053	P-8-2	Red, 8"	EACH	4.45
885-0011	P-12-0	Black, 12"	EACH	4.45
885-0012	P-12-2	Red, 12"	EACH	4.45
885-0013	P-18-0	Black, 18"	EACH	4.45
885-0054	P-18-2	Red, 18"	EACH	4.45
885-0055	P-24-0	Black, 24"	EACH	4.45
885-0056	P-24-2	Red, 24"	EACH	4.45
885-0057	P-36-0	Black, 36"	EACH	4.45
885-0058	P-36-2	Red, 36"	EACH	4.45

Test Lead Holder



Stock No.	Mfr.'s Type	Color	Dia.	Slots	EACH
885-0382	1508	Orange	0.210"	14	5.85
885-4408	4408	Black	0.320"	10	5.85
885-0631	2708	Blue	0.450"	9	5.85


Stacking Banana Plug to Stacking Pin Tip Plug



Adapts to equipment using banana jacks and pin jacks. Banana plug and pin tip allow vertical stackup. **1st End:** Stacking banana plug. Brass body, beryllium copper spring, nickel plated. **Insulation:** Polypropylene. **Wire:** 20 AWG, 41 x 36 t.c., PVC insulated, 2.2 (.087) O.D. **2nd End:** Stacking pin tip plug. Brass body, beryllium copper spring, gold plated. **Insulation:** Polypropylene. **Rating:** 3000 VDC, 5 amps, +55°C (+131°F) max.

885-1129	1126-12-0	Black, 12"	EACH	4.35
885-1130	1126-12-2	Red, 12"	EACH	4.35
885-1131	1126-18-0	Black, 18"	EACH	4.35
885-1132	1126-18-2	Red, 18"	EACH	4.35
885-1133	1126-24-0	Black, 24"	EACH	4.35
885-1134	1126-24-2	Red, 24"	EACH	4.35
885-1135	1126-36-0	Black, 36"	EACH	4.35
885-1136	1126-36-2	Red, 36"	EACH	4.35
885-1137	1126-48-0	Black, 48"	EACH	4.55
885-1138	1126-48-2	Red, 48"	EACH	4.55
885-1139	1126-60-0	Black, 60"	EACH	4.55
885-1140	1126-60-2	Red, 60"	EACH	4.55

Banana Plug to In-Line Banana Jack



Dual purpose. Insulates all hot leads when used as an extension cord. Endless extension couplings possible with any banana plug patch cord. **1st End:** Banana plug. Brass body, beryllium copper spring, nickel plated. **Insulation:** Polypropylene. **Wire:** 18 AWG, 65 x 36 t.c., PVC insulated, 3.7 (.144) O.D. **2nd End:** In-line banana jack. Brass, nickel plated. **Insulation:** Polypropylene. **Rating:** 5000 VDC, 15 amps, +55°C (+131°F) max.

885-4700	4702-12-0	Black, 12"	EACH	4.95
885-4701	4702-12-2	Red, 12"	EACH	4.95
885-4702	4702-18-0	Black, 18"	EACH	4.95
885-4703	4702-18-2	Red, 18"	EACH	4.95
885-4704	4702-24-0	Black, 24"	EACH	4.95
885-4705	4702-24-2	Red, 24"	EACH	4.95
885-4706	4702-36-0	Black, 36"	EACH	4.95
885-4707	4702-36-2	Red, 36"	EACH	4.95
885-4708	4702-48-0	Black, 48"	EACH	5.15
885-4709	4702-48-2	Red, 48"	EACH	5.15
885-4710	4702-60-0	Black, 60"	EACH	5.15
885-4711	4702-60-2	Red, 60"	EACH	5.15


Extension Stacking Banana Plug Each End



Dual purpose. Insulates all hot leads when used as an extension cord. Endless extension couplings possible with any banana plug patch cord. **1st End:** Extension stacking banana plug. Brass body, beryllium copper spring, nickel plated. **Insulation:** Polypropylene. **Wire:** 18 AWG, 65 x 36 t.c., PVC insulated, 3.7 (.144) O.D. **2nd End:** Extension stacking banana plug. Brass body, beryllium copper spring, nickel plated. **Insulation:** Polypropylene. **Rating:** 5000 VDC, 15 amps, +55°C (+131°F) max.

885-4008	HB-12-0	Black, 12"	EACH	5.85
885-4009	HB-12-2	Red, 12"	EACH	5.85
885-4010	HB-24-0	Black, 24"	EACH	5.85
885-4011	HB-24-2	Red, 24"	EACH	5.85
885-4012	HB-36-0	Black, 36"	EACH	5.85
885-4013	HB-36-2	Red, 36"	EACH	5.85
885-9984	HB-48-0	Black, 48"	EACH	6.25
885-9983	HB-48-2	Red, 48"	EACH	6.25

Alligator Clip to Stacking Banana



1st End: Alligator clip. Steel, nickel plated. Vinyl boot. **Wire:** 18 AWG, 65 x 36 t.c., PVC insulated, 3.7 (.144) O.D. **2nd End:** Stacking banana plug. Brass body, beryllium copper, gold plated. **Insulation:** Polypropylene. **Rating:** 150 VAC, 5 amps, +50°C (+122°F) max.

885-1166	1166-4-0	Black, 4"	EACH	4.10
885-1167	1166-4-2	Red, 4"	EACH	4.10
885-1168	1166-8-0	Black, 8"	EACH	4.10
885-1169	1166-8-2	Red, 8"	EACH	4.10
885-4040	1166-12-0	Black, 12"	EACH	4.10
885-4041	1166-12-2	Red, 12"	EACH	4.10
885-4042	1166-24-0	Black, 24"	EACH	4.10