



FEATURES:

- Ideal for providing a temporary jumper wire between surface mount devices.

MATERIALS:

SMD Grabber[®] test clip

Contact - Stainless Steel

Spring – Stainless Steel

Cap – Glass filled nylon. Color matches color of wire

Barrel – Glass filled nylon. Color matches color of wire

Marking: “POMONA GRABBER[®]”

Finish: Gold plated

Wire: 22 AWG, PVC insulated

Marking: “Model 5301”

RATINGS:

Operating Temperature: +102°C. (+216°F.) Max.

Voltage: Hand-held testing 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 150 WVDC Max.

Current: .5 Amperes

ORDERING INFORMATION: Model 5301-XX-*

XX= Length in inches

*= Color, -0 Black, -2 Red

Ordering Example: 5301-12-2 Indicates 12”, color is red.

5521 Kit contains 10 pieces of model 5301-24, 1 each of 10 colors. 5303-36-* SMD Grabber test clip one end only.

All dimensions are in inches and metric (m,m). All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS **90664** (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com