


**Models 6883, 6884
Dual Binding Posts with Base (raised base)**



Model 6883 Dual Binding Posts



Model 6884 Dual Binding Posts with Raised Base



Use as an ideal interconnect

Features

- 5-way binding post with 0.154" cross-hole that accepts up to 12 AWG wire and standard banana plugs.
- Posts are spaced at the standard 3/4" inch spacing to mate to dual banana plugs.
- 30 A current rating.

Materials

- Posts are made of nickel-plated brass.
- Insulators and base are made of nylon.

Ordering Information

Model: 6883, 6884

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

Specifications

Current rating	30 A at low voltage
Voltage rating	500 V dc at low current
Wire gauge	Up to 12 AWG
Operating temperature	Up to 70 °C

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.