



### FEATURES:

- Mate to Model #3542, 4773 or any other standard .08 inch pin jack.
- Ideal for use as jumper wires on chassis boxes.

### MATERIALS:

Conn: Pin Tip Plug

Material: Brass Per QQ-B-626, Alloy 360, ½ Hard.

Finish: Gold plated per MIL-G-45204, Type II, Class 00 over electroless nickel per MIL-C-26074, Class I, 200/300 microinches.

Insulation: Polypropylene molded to plug body and wire.

Color: Matches color of wire.

Marking: "POMONA ELECTRONICS CALIF."

Wire: 22 AWG, stranding 19 x 34, t.c., PVC insulated, 1.63 (.064) O.D.

Color: See Ordering Information.

Marking: "POMONA PT080-XX"

### RATINGS:

Operating Temperature: +55°C. (+131°F.) Max.

Operating Voltage: 1000 WVDC

Current: 3 Amperes Cont.

### ORDERING INFORMATION: Model PT080-XX-\*

XX = Cable Lengths, Standard Lengths: 4" (102), 8" (305), 18" (457), 24" (610), 36" (914), 48" (1219) & 60" (1524). Additional lengths can be quoted upon request.

\*= Color, -0 Black, -2 Red

Ordering Example: PT080-60-2 Indicates 60" in length, Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[PT080-8-2](#) [PT080-8-0](#)