



FEATURES:

- Mate to Model #3542, 4773 or any other standard .08 inch pin jack.
- Ideal for use as jumper wires on chassis boxes.

MATERIALS:

Conn: Pin Tip Plug

Material: Brass Per QQ-B-626, Alloy 360, ½ Hard.

Finish: Gold plated per MIL-G-45204, Type II, Class 00 over electroless nickel per MIL-C-26074, Class I, 200/300 microinches.

Insulation: Polypropylene molded to plug body and wire.

Color: Matches color of wire.

Marking: "POMONA ELECTRONICS CALIF."

Wire: 22 AWG, stranding 19 x 34, t.c., PVC insulated, 1.63 (.064) O.D.

Color: See Ordering Information.

Marking: "POMONA PT080-XX"

RATINGS:

Operating Temperature: +55°C (+131°F) Max

Operating Voltage: 1000 WVDC

Current: 3 Amperes Cont.

ORDERING INFORMATION: Model PT080-XX-*

XX = Cable Lengths, Standard Lengths: 8" (203mm)

Additional lengths can be quoted upon request.

*= Color, -0 Black, -2 Red

Ordering Example: PT080-8-2, Indicates 8" in length, Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA