

6

5

4

3

2

1

MATERIAL AND FINISH:

Insulator: Polycarbonate, UL-94V-0 rated

Contacts: Brass, Nickel plated




ELECTRICAL SPECIFICATIONS:

Current rating: 10 A

Voltage rating: 250 VAC

Current rating: 15 A

Voltage rating: 250 VAC

RECOMMENDED
PANEL CUTOUT

ORDERING CODE:

42R02-1 1 2 3

1 = TERMINAL OPTIONS



1 = .187(4.8)

2 = .250(6.3)

2 = COLOR

1 = BLACK

2 = GRAY

3 = ELECTRICAL CIRCUIT
CONFIGURATION1 = 15A 250V 120°C
2+GROUND2 = 15A 250V 70°C
2+GROUND4 = 15A 250V 70°C
2 POLETOLERANCE
UNLESS OTHERWISE SPECIFIED
X ± 1
X.X ± 0.4
X.XX ± 0.20**Power Dynamics, Inc.**

Phone: 973 560-0019 Whippany, New Jersey Fax: 973 560-0070

PART: IEC 60320 C14 APPL. INLET; QUICK CONNECT
TERMINALS; SIDE FLANGED, PANEL MOUNT

PART #: 42R02-1XXX

SHEET
1 of 1

SIZE: A

SCALE: NTS

ALL DIMENSIONS FOR REFERENCE ONLY
DIMENSIONS ARE IN MILLIMETERS

REV:

RoHS
COMPLIANT

REVISIONS

REV	DATE	CHANGE	CHK	APPR