

R2F SM Plug / R2F SM Plug Patchcord 5m


Issue

18/12/2009

Page

1/1

Dimension in mm



GENERAL

Type:	<i>End1</i> R2F Plug, for 2 Singlemode channels. Screw thread coupling device (to be installed with a 100 Ncm torque wrench). Vinyl protective cap.	<i>End2</i> R2F Plug, for 2 Singlemode channels. Screw thread coupling device (to be installed with a 100 Ncm torque wrench). Vinyl protective cap.
Cable:	SM 9/125 field cable	
Identification:	Self-laminated label, RADIAL / F760 885 620-05 /MO nb.	

CHARACTERISTICS

(depending on cable construction)

	<i>End 1 (R2F)</i>	<i>End 2 (R2F)</i>
Optical : Cable assembly		
Insertion Loss (@ 1310 nm)		1.00 dB max (method 6)
Return Loss (@ 1310 nm)		RL > 45dB (method 7)
acc. to IEC 61300-3-4		
Mechanical :		
Endurance	500 mating cycles	500 mating cycles
Tensile load	up to 800 N (depending on cable)	up to 800 N (depending on cable)
Vibration	Acc. To IEC 61300.2.1	Acc. To IEC 61300.2.1
Environmental:		
Protection	IP67 (plugged)	IP67 (plugged)
Operating temperature	-40°C to + 85°C	-40°C to + 85°C
2002/95/EC (RoHS)	Compliant	

CREATION

N°PEN :
Name: MM
Date: 18/12/2009
Appr.: FP

Issue

Revisions

Name

Appr.

RADIAL®

101, rue P. Hoffmann
93116 ROSNY/BOIS
FRANCE
Tel : (33) 0149353535
Fax : (33) 0148546363