

R2F MM Plug / R2F MM Plug Patchcord 5m


Issue

18/12/2009

Page

1/1

Dimension in mm



GENERAL

	<i>End1</i>	<i>End2</i>
Type:	R2F Plug, for 2 Multimode channels. Screw thread coupling device (to be installed with a 100 Ncm torque wrench). Vinyl protective cap.	R2F Plug, for 2 Multimode channels. Screw thread coupling device (to be installed with a 100 Ncm torque wrench). Vinyl protective cap.
Cable:	Field cable MM 50/125	
Identification:	Self-laminated label, RADIAL / F760 888 620-05 /MO nb.	

CHARACTERISTICS

(depending on cable construction)

	<i>End 1 (R2F)</i>	<i>End 2 (R2F)</i>
Optical : Cable assembly Insertion Loss (@ 850 nm) acc. to IEC 61300-3-4	1.50 dB	(method 6)
Mechanical : Endurance Tensile load Vibration	500 mating cycles up to 800 N (depending on cable) Acc. To IEC 61300.2.1	500 mating cycles up to 800 N (depending on cable) Acc. To IEC 61300.2.1
Environmental: Protection Operating temperature	IP67 (plugged) -40°C to + 85°C	IP67 (plugged) -40°C to + 85°C
2002/95/EC (RoHS)	Compliant	

CREATION

N°PEN :
Name: MM
Date: 18/12/2009
Appr.: FP

Issue

Revisions

Name

Appr.

RADIAL®

101, rue P. Hoffmann
93116 ROSNY/BOIS
FRANCE
Tel : (33) 0149353535
Fax : (33) 0148546363