

# R1EX25008ASA00A

[Datasheet](#)

**EOL Products**

**EOL Products:**  
A certain prescribed period of time has passed since EOL was announced for these products, and production has been discontinued.



Product Info	Design Support	Documentation	Ordering
--------------	----------------	---------------	----------





## Product Spec

	Basic Information	Package	Packing
--	-------------------	---------	---------

Basic Information		
Organization (bit)	x 8	
Star Product	-	
Family/ Series	Serial EEPROM	
Interface	SPI bus	
Memory Capacity (Kbit)	8	
Organization (word)	1	
Package Type	SOP(8)	
Supply voltage (V)	1.8 to 5.5	
Operating temperature (°C)	-40 to 85	
Application	Consumer	
Production Status	EOL	
Clock frequency (Hz)	5M/3M	

Package	
Name	SOP
JEITA code	P-SOP8-3.9x4.89-1.27
Previous code	FP-8DBV
Renesas code	PRSP0008DF-B
Terminal count	8
Terminal pitch (mm)	1.27 mm
Dimensions (mm)	3.9x4.89

Mass (g) [TYP,]	0.08
Drawing Link	 <a href="#">prsp0008df_b</a>
Mount pad	 <a href="#">fig0001e</a>
Terminal material - Base	Cu alloy
Terminal material - Surface	Ni/Pd/Au

Packing	
Container	Tape No dry pack  <a href="#">tape-NSP</a>
	Tape Simple pack  <a href="#">tape-SP</a>
	Tape  <a href="#">tape2125</a>  <a href="#">tape2124</a>

[Find similar products](#)

## Need More Help ?

[Contact Us](#) [Website Feedback](#)

[Distributors](#) [Videos](#)

[Forums](#) [Newsletter](#)


## Others


[Mobile App](#) [Privacy Policy](#)


[Legal](#)

[Sitemap](#)

## Follow Us

 [Facebook](#)

 [Twitter](#)

 [YouTube](#)