

i.L. = Clearance width

Supply includes:

Enclosure, cover with all-round foamed-in PU seal and cover screws, including plastic bushes.

	Packs of	KL terminal boxes, stainless steel						Page
Width (B1) in mm		150	300	200	300	400	300	
Height (H1) in mm		150	150	200	200	200	300	
Depth (T1) in mm		80	80	80	80	120	120	
Model No. KL	1	1521.010	1522.010	1523.010	1524.010	1525.010	1526.010	
B2 = Clearance opening width		132	282	182	282	382	282	
B3 = Cover width		148	298	198	298	398	298	
B4 = Clearance width between profile strips		109	259	159	259	359	259	
B5 = Hole-centre distance of profile strips		125	275	175	275	375	275	
H2 = Clearance opening height		132	132	182	182	182	282	
H3 = Cover height		148	148	198	198	198	298	
H4 = Clearance height between profile strips		100	100	150	150	150	250	
Weight (kg)		1.3	1.8	1.8	2.4	3.6	3.69	
Cover screws		4	4	4	4	4	4	

Accessories

Mounting plate KL	1	1560.700	1561.700	1562.700	1563.700	1564.700	1567.700	965
Wall mounting bracket KL	4	1594.000						299
Wall angle SZ	1	2583.000						299
Pole clamp SZ	1	2584.000						962
Support rails TS 35/7.5 SZ	10	2314.000	2316.000	2315.000	2316.000	2317.000	2316.000	983



KL stainless steel terminal boxes have the following approvals:

- UL
- CSA
- TÜV
- Germanischer Lloyd
- Norske Veritas
- Russian Maritime Register of Shipping
- Lloyds Register of Shipping
- Bureau Veritas
- VDE



+ **Other accessories:**

see page 296 – 299
and page 876/877
or refer to index.

Material:

Stainless steel 1.4301
Box: 1.25 mm
Cover: 1.25 mm

Surface finish:

Box and cover:
Brushed

Protection category:

IP 66 to EN 60 529/10.91
Complies with NEMA 4x



Wall mounting bracket
For secure mounting to the wall.
Model No. see page 299.




Housing coupling
For attaching the 120 mm deep KL to the support arm system.
Model No. see page 277.




Mounting plate
For component mounting even outside of the box.
Model No. see page 965.



BG 1558.010 / BG 1559.010



BG 1583.010 / BG 1584.010 / BG 1585.010



i.L. = Clearance width



Supply includes:

Enclosure with 1 support rail TS 35/7.5,
Lid with foamed seal,
180° hinges,
with quick-release fasteners.

	Packs of						Page
Width in mm		200	300	400	400	600	
Height in mm		300	300	300	200	200	
Depth in mm		80	80	80	123	123	
Model No. BG	1	1583.010	1584.010	1585.010	1558.010	1559.010	
Weight (kg)		2.8	3.7	4.5	4.5	6.0	
Accessories							
Wall mounting bracket KL	4	1594.000			1594.000		299
Pole clamp SZ	1	2584.000			2584.000		962
Condensate discharge SZ	6	2459.000			2459.000		900



BG stainless steel bus enclosures have the following approvals:

- UL
- CSA
- TÜV
- DNV
- Russian Maritime Register of Shipping
- Lloyds Register of Shipping
- Bureau Veritas
- VDE



+ **Other accessories:**

see page 296 – 299
and page 876/877
or refer to index.

Material:

Stainless steel 1.4301, brushed

Protection category:

IP 66 to EN 60529/10.91

Modification:

Viewing window for I/O displays and holes for screw connections or other designs available on request.



Wall mounting bracket
For secure attachment of enclosures.
Model No. see page 299.



Pole clamp
For fastening to round or square poles.
Model No. see page 962.



EMC cable glands
With special ring for 360° contact.
Model No. see page 894.