


HORIZONTAL & MODIFIED HEADERS

(2.00 mm) .0787" PITCH • MMT/MTMM SERIES



MMT/MTMM

Board Mates:

CLT, SQT*, SQW, ESQT,
TLE, SMM, MMS

Cable Mates:

TCSD

*Important Note:

SQT will not mate to the
MMT -02 lead style.

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over
50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 $^{\circ}$ C to +105 $^{\circ}$ C with Tin;
-55 $^{\circ}$ C to +125 $^{\circ}$ C with Gold

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity (MMT):

(0.10 mm) .004" max (02-25)

(0.15 mm) .006" max (26-36)*

*(.004" stencil solution
may be available; contact
ipg@samtec.com)

MMT	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OPTION
		02 thru 36				
			-01 = (3.20 mm) .126" post	-F = Gold flash on post, Matte Tin on tail	-SH = Single Row	-K = (4.00 mm) .157" DIA Polyimide Film Pick & Place Pad (3 positions min.)
			-02 = (4.45 mm) .175" post	-L = 10 μ " (0.25 μ m) Gold post, Matte Tin on tail	-DH = Double Row	-P = Pick & Place Pad (2 positions min.)
				-T = Matte Tin	-MT = Double Row Mixed Technology	-“XXX” = Polarized Position Specify position of omitted pin
						-TR = Tape & Reel
						-FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)

ALSO AVAILABLE
Contact Samtec

Alignment pins
Locking clips
Molded pick &
place pads

MTMM	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	POST HEIGHT	OPTION
		01 thru 50					
			Specify LEAD STYLE from chart	-F = Gold flash on post, Matte Tin on tail	-S = Single Row	-“XXX” = Post Height in inches (0.13 mm) .005" increments	-“XXX” = Polarized Position Specify position of omitted pin
				-L = 10 μ " (0.25 μ m) Gold post, Matte Tin on tail	-D = Double Row	Example: -070 = (1.78 mm) .070"	
				-T = Matte Tin	-Q = Quad Row		

LEAD STYLE	OAL
-02	(6.48) .255
-03	(7.67) .302
-04	(8.20) .323
-05	(9.58) .377
-06	(10.08) .397
-07	(11.58) .456
-08	(12.09) .476
-09	(13.59) .535
-10	(14.10) .555
-11	(15.09) .594
-12	(15.60) .614
-13	(17.09) .673
-14	(19.08) .751
-15	(21.08) .830

Note:

Some lengths, styles and
options are non-standard,
non-returnable.

samtec.com?MMT or samtec.com?MTMM

F-226