

(2.00 mm) .0787"

SQW SERIES


COST-EFFECTIVE RUGGED SOCKETS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?SQW

- Insulator Material:** Black Liquid Crystal Polymer
- Contact Material:** Phosphor Bronze
- Plating:** Sn or Au over 50 μ" (1.27 μm) Ni
- Current Rating (SQW/TMMH):** 3.8 A per pin (2 pins powered)
- Voltage Rating:** 281 VAC mated with TMM; 250 VAC mated with TMMH
- Operating Temp Range:** -55 °C to +125 °C
- Insertion Depth:** (2.62 mm) .103" to (5.03 mm) .198" with (0.38 mm) .015" wipe
- Max Cycles:** 100 with 10 μ" (0.25 μm) Au
- RoHS Compliant:** Yes

- Board Mates:** TMMH, TMM, MTMM, MMT, TW, TSH, LTMM, PTT
- Cable Mates:** TCMD




PROCESSING

- Lead-Free Solderable:** Yes, for -D & -D-VS (Wave only for -T, -Q, -5 & -6)
- SMT Lead Coplanarity:** (0.10 mm) .004" max (02-10) (0.15 mm) .006" max (11-50)* (.004" stencil solution may be available; contact IPG@samtec.com)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications. Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.