




**Rack ATS, 15A, 100/120V, (2)5-15 in,  
(8)5-15 out**

**Part Number:** AP7750

**Output**

|                                      |                |                                                                                      |
|--------------------------------------|----------------|--------------------------------------------------------------------------------------|
| Nominal Output Voltage               | 100V,120V      |  |
| Maximum Total Current Draw per Phase | 15A            |                                                                                      |
| Output Connections                   | (8) NEMA 5-15R |                                                                                      |

**Input**

|                                  |                      |                                                                                       |
|----------------------------------|----------------------|---------------------------------------------------------------------------------------|
| Nominal Input Voltage            | 100V,120V            |  |
| Input Frequency                  | 50/60 Hz             |                                                                                       |
| Regulatory Derated Input Current | 12A                  |                                                                                       |
| Input Connections                | NEMA 5-15P           |                                                                                       |
| Cord Length                      | 8 feet (2.44 meters) |                                                                                       |
| Number of Power Cords            | 2                    |                                                                                       |
| Acceptable Input Voltage         | 100-125 VAC          |                                                                                       |
| Maximum Input Current per phase  | 15A                  |                                                                                       |
| Load Capacity                    | 1440 VA              |                                                                                       |

## Physical

|                 |                       |
|-----------------|-----------------------|
| Net Weight      | 9.75 lbs. (4.43 kg)   |
| Maximum Height  | 1.75 inches (44 mm)   |
| Maximum Width   | 17.00 inches (432 mm) |
| Maximum depth   | 9.00 inches (229 mm)  |
| Shipping Weight | 16.25 lbs. (7.39 kg)  |
| Shipping Height | 2.75 inches (70 mm)   |
| Shipping Width  | 23.50 inches (597 mm) |
| Shipping Depth  | 17.50 inches (445 mm) |
| Color           | Black                 |

## Environmental

|                             |                               |
|-----------------------------|-------------------------------|
| Operating Environment       | 23 - 113 °F (-5 - 45 °C)      |
| Operating Relative Humidity | 0 - 95%                       |
| Operating Elevation         | 0-10000 feet (0-3000 meters)  |
| Storage Temperature         | -13 - 149 °F (-25 - 65 °C)    |
| Storage Relative Humidity   | 0 - 95%                       |
| Storage Elevation           | 0-50000 feet (0-15000 meters) |

## Conformance

|                      |                                               |
|----------------------|-----------------------------------------------|
| Regulatory Approvals | cUL Listed,FCC Part 15 Class A,UL Listed,VCCI |
| Standard Warranty    | 2 years repair or replace                     |

\*Estimated Resale Price - Without Tax/VAT