

**Item # ZB4BW0B11, Base, Contact, & Light Module**

Base, Contact, & Light Module

Specifications

Product Description	Base, Contact, & Light Module
Ampere Rating	10A
Terminal Type	Screw Clamp
Wire Range	min: 1x0.22; max: 2x16AWG
Tightening Torque	0.8 Nm
Light Module Electrical Consumption	24V = 18mA; 120/240V = 14mA
CE	Yes
RoHS	Yes
Contact Configuration	1 N.O.
Contact Material	Silver Alloy
Light Module Supply Voltage	n/a
Light Module Type	LED (White)
Light Module Voltage	24Vac/dc
Utilization Category	AC-15; DC-13
Used On	ZB4 Metal Operators
Application	standard