

# SiT1602AC-1-18E-ND

## Part Family

"SiT1602"

## Revision Letter

"A" is the revision

## Temperature Range

"C" Commercial, -20 to 70°C  
"I" Industrial, -40 to 85°C

## Output Drive Strength

"—" Default (datasheet limits)  
*See Tables 1 to 5 for rise/fall times*

|     |     |
|-----|-----|
| "L" | "T" |
| "A" | "E" |
| "R" | "U" |
| "B" | "F" |

## Package Size

|     |              |
|-----|--------------|
| "7" | 2.0 x 1.6 mm |
| "1" | 2.5 x 2.0 mm |
| "2" | 3.2 x 2.5 mm |
| "3" | 5.0 x 3.2 mm |
| "8" | 7.0 x 5.0 mm |

## Feature Pin

"E" for Output Enable  
"S" for Standby

## Supply Voltage

"18" for 1.8V  $\pm 10\%$   
"25" for 2.5V  $\pm 10\%$   
"28" for 2.8V  $\pm 10\%$   
"30" for 3.0V  $\pm 10\%$   
"33" for 3.3V  $\pm 10\%$   
"XX" for 2.25V to 3.63V

\*The frequency stability defaults to the lowest available programming option in house. This will be noted on the individual part number product page.

\*Call Digi-Key and a Sales Representative will enter your desired frequency. For online orders, you may enter it into the web notes.

*Programmable parts are non-cancelable and non-returnable*