

Thursday, 29 November 2012



www.sks-kontakt.de

News contact sitemap Login

main menu

- home
- products
- skills
- download

online catalogue T&M

- clamp-type test probes
- crocodile clips
- test probes
- oscilloscope test probes
- measuring leads
- plugs
- sockets
 - ▶ 2 mm system
 - ▶ 2 mm safety system
 - ▶ 4 mm system
 - ▶ 4 mm safety system
- sets
- miscellaneous

company

- portrait
- corporate association
- location maps
- fairs and exhibitions
- jobs
- imprint
- terms and conditions

Home ▶ sockets ▶ sockets ▶ KUN 10

KUN 10

datasheet for KUN 10
article number: 930189101



View Full-Size Image

product description:	order number: 930 189-101
description:	Insulated coupling for a 4 mm diameter plug and screw connection up to cable cross-section of 1.5 mm ² . Tin-plated brass socket. The socket is screwed into the insulated handle.
typ:	KUN 10 rot/red
system:	4mm system
order number:	930 189-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
norm	IEC 61010
type of contact:	4 mm socket (unsprung)
type of termination:	screw
rated voltage:	30 VAC / 60 VDC
rated current:	16 A
Please consider derating curve!	
contact resistance:	10 mOhm
material	
contact material:	brass
contact surface material:	tin
housing material:	PS
environmental conditions:	
temperature range:	-25 °C to +70 °C
inflammable class:	
housing (basic material):	UL 94 HB
drawing	

search online catalogue



Search

Messetermine

SPS/IPC/DRIVES
29. 11. 2012 - 29. 11. 2012

Newsletter Anmeldung

Test & Measurement

QR-Code

