

main menue



home

test & measurement

products

skills

download

online catalogue T&M

clamp-type test probes

crocodile clips

test probes

oscilloscope test probes

measuring leads

plugs

sockets

- ▶ 2 mm system
- ▶ 2 mm safety system
- ▶ 4 mm system
- ▶ 4 mm safety system

sets

miscellaneous

company

portrait

corporate association

location maps

fairs and exhibitions

jobs

imprint

terms and conditions

Home ▶ sockets ▶ sockets ▶ MKU 1

MKU 1

 datasheet for MKU 1
 article number: 930320101


View Full-Size Image



search online catalogue

Search

Search

Messetermine

No events

QR-Code



product description:	order number: 930 320-101
description:	2 mm diameter miniature coupling, insulated, tin-plated copper beryllium contact spring with solder connection. Flexible, shatter-proof insulated sleeve. For making up connecting leads with a maximum external diameter of 2 mm.
typ:	MKU 1 rot/red
order number:	930 320-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
type of contact:	spring-loaded socket 2 mm
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	6 A
Please consider derating curve!	
contact resistance:	6 mOhm
material	
contact material:	contact spring: copper - beryllium
contact surface material:	tin
housing material:	PVC-P
drawing	