



main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
test probes
oscilloscope test probes
measuring leads
plugs
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm sliding sleeve system
 ▶ 4 mm safety system
sockets
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ plugs ▶ plugs ▶ BUELA 30 K

BUELA 30 K

datasheet for BUELA 30 K
article number: 930727101



View Full-Size Image



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:	order number: 930 727-101
description:	Multiple-spring wire plug, shatter-proof, flexible insulated sleeve with transverse hole. The tapering sleeve end also serves as kinking protection for the lead. Solder connection up to maximum cable cross-section of 2.5 mm². Nickel-plated brass contact material.
typ:	BUELA 30 K rot/red
system:	4mm system
order number:	930 727-101
color	
other color versions:	     
technical data	
measurement category acc. to IEC 61010:	CAT I
pin dimensions	4 mm
type of contact:	pin (spring loaded)
type of termination:	solder
rated voltage:	30 VAC / 60 VDC
rated current:	30 A
Please consider derating curve!	
contact resistance:	3 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PVC - P
environmental conditions:	
temperature range:	-25 °C to +70 °C
drawing	
	