

main menu



home
 test & measurement
 products
 skills
 download

online catalogue T&M

clamp-type test probes

- ▶ 0,64 mm system
- ▶ 2 mm system
- ▶ 2 mm Sicherheitssystem
- ▶ 4 mm system
- ▶ 4 mm sliding sleeve system
- ▶ 4 mm safety system

crocodile clips

test probes

oscilloscope test probes

measuring leads

plugs

sockets

sets

miscellaneous

company

portrait

corporate association

location maps

fairs and exhibitions

jobs

imprint

terms and conditions

Home ▶ clamp-type test probes ▶ clamp-type test probe ▶ KLEPS 2900

KLEPS 2900

datasheet for KLEPS 2900
 article number: 972309101



View Full-Size Image



search online catalogue

Search

Search

Messetermine

SPS/IPC/DRIVES
 24. 11. 2016 - 24.
 11. 2016

QR-Code



product description:	order number: 972 309-101
description:	Safety clamp-type test probe with rigid hook to ensure secure clamping of eyes, pins, wires and boards. 4 mm brass socket connection. Connects with safety measuring leads.
typ:	KLEPS 2900 rot/red
system:	4 mm safety system
order number:	972 309-101
clamping range:	5.5 mm
clamping typ:	contact hook
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT III
type of termination:	4 mm socket (unsprung)
rated voltage:	AC/DC 1000 V
rated current:	20 A
Please consider derating curve!	
contact resistance:	10 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PBT
environmental conditions:	
temperature range:	-25 °C to +80 °C
flammable class:	
housing (basic material):	UL 94 HB
drawing	
	