

531-492


els

TK 1313





TK 1313  
Ample connecting space,  
up to 7 Pg 21  
entries -  
an allrounder  
in the  
TK series.



| Important information   |          |      |
|-------------------------|----------|------|
| Description             | Ref. No. | Page |
| Mounting plate          | 195-005  | 61   |
| Mounting rail TS 15/106 | Z-632    | 61   |
| Standard rail NS 35/106 | Z-658    | 61   |
| Hinge kit               | 190-002  | 61   |
| Wall plate set          | 194-001  | 61   |




Matching hinge kits  
including drilling  
templates are  
available as  
accessories for all  
TK enclosures.

| Type                                | Side Walls | Pg Knockouts                                                                        | Inside Height | Ref. No. | Unit |
|-------------------------------------|------------|-------------------------------------------------------------------------------------|---------------|----------|------|
| POLYSTYRENE - COVER GREY RAL 7035   |            |                                                                                     |               |          |      |
| PS 1313- 7                          | with Pg    |    | 63 mm         | 115-405  | 14/2 |
| PS 1313-10                          | with Pg    |                                                                                     | 87 mm         | 115-905  | 8/2  |
| PS 1313- 7-o                        | smooth     |                                                                                     | 63 mm         | 110-405  | 14/2 |
| PS 1313-10-o                        | smooth     |                                                                                     | 87 mm         | 110-905  | 8/2  |
| POLYSTYRENE - COVER TRANSPARENT     |            |                                                                                     |               |          |      |
| PS 1313- 7-t                        | withPg     |    | 63 mm         | 116-005  | 14/2 |
| PS 1313-10-t                        | with Pg    |                                                                                     | 87 mm         | 116-505  | 8/2  |
| PS 1313- 7-to                       | smooth     |                                                                                     | 63 mm         | 111-005  | 14/2 |
| PS 1313-10-to                       | smooth     |                                                                                     | 87 mm         | 111-505  | 8/2  |
| POLYCARBONATE - COVER GREY RAL 7035 |            |                                                                                     |               |          |      |
| PC 1313- 7                          | with Pg    |  | 63 mm         | 125-405  | 14/2 |
| PC 1313-10                          | with Pg    |                                                                                     | 87 mm         | 125-905  | 8/2  |
| POLYCARBONATE - COVER TRANSPARENT   |            |                                                                                     |               |          |      |
| PC 1313- 7-t                        | with Pg    |  | 63 mm         | 135-005  | 14/2 |
| PC 1313-10-t                        | with Pg    |                                                                                     | 87 mm         | 135-505  | 8/2  |

**TK 1313**  
**Empty**  
**Enclosure**  
**130 x 130<sup>mm</sup>**  
**Type of**  
**Protection**  
**IP 66**

**Knockouts:**     = Pg 16/11     = Pg 16     = Pg 21/16     = Pg 29/21



Max. number  
of Pg drill holes  
per box side

| Pg   | A  | B  |
|------|----|----|
| 7    | 10 | 10 |
| 9    | 8  | 8  |
| 11   | 8  | 8  |
| 13.5 | 3  | 3  |
| 16   | 3  | 3  |
| 21   | 2  | 2  |
| 29   | 2  | 2  |
| 36   | -  | -  |

All dimensions in millimeters