

Junction Boxes

HP 70 to HP 190



IP 55



Overview of the characteristics of this HP series

Use	Weak acid	Strong acid	Weak alkali	Strong alkali	Alcohol	Benzin	Benzene	Mineral oil	Diesel	Ammonia	Vegetable oil	Animal oil	Free of halogen, heavy metal, PVC and silicone
HP-Enclosures	●	▶	●	▶	●	▶	●	▶	●	▶	●	▶	yes








- = resistant
- ▶ = partially-resistant
- ⊗ = not-resistant



- 6 sizes
- Assembly on wood or other inflammable materials
- Assembled stepped nipple
- Connection diameter 1.5 mm² to 10 mm²
- Entry positions also suitable for metric add-on accessories 2 to 10 mm²

Suitable for the installation

- In damp and wet areas and rooms
- In buildings where there are crowds of people
- In temporary buildings, vehicles and caravans

		Description	Order No.	Packing Qty
HP 70 75 x 75 x 42 mm Interior dimensions: 68 x 68 x 38 mm 	IP 55   Entries	Junction box according to E DIN IEC 60998-2-5, $U_i=400$ V, 3 recessed stepped nipples, and 2 loose ones enclosed, seal range 5 to 16 mm, for terminals up to 2.5 mm ²		
		HP 70 - L grey, without terminals	320 970 01	60/1
HP 80 85 x 85 x 42 mm Interior dimensions: 78 x 78 x 38 mm 	IP 55   Entries	Junction box according to E DIN IEC 60998-2-5, $U_i=400$ V, 7 recessed stepped nipples, seal range 5 to 16 mm, for terminals up to 2.5 mm ²		
		HP 80 - L grey, without terminals	322 980 01	50/1
HP 90 90 x 90 x 45 mm Interior dimensions: 82 x 82 x 38 mm 	IP 55   Entries	Junction box according to E DIN IEC 60998-2-5, $U_i=400$ V, 7 recessed stepped nipples, seal range 5 to 16 mm, for terminals up to 4 mm ²		
		HP 90 - L grey, without terminals	325 990 01	40/1
HP 100 113 x 113 x 58 mm Interior dimensions: 103.5 x 103.5 x 32 mm 	IP 55   Entries	Junction box according to E DIN IEC 60998-2-5, $U_i=690$ V, 7 recessed stepped nipples, seal range 5 to 21 mm, for terminals up to 10 mm ²		
		HP 100 - L grey, without terminals	326 900 01	20/1
HP 150 164 x 119 x 77 mm Interior dimensions: 155 x 110 x 70 mm 	IP 55   Entries	Junction box $U_i=690$ V, 10 recessed stepped nipples, seal range 5 to 21 mm		
		HP 150 - L grey, without terminals	326 950 01	12/1
HP 190 199 x 149 x 77 mm Interior dimensions: 190 x 140 x 70 mm 	IP 55   Entries	Junction box $U_i=690$ V, 10 recessed stepped nipples, seal range 13 to 26.5 mm		
		HP 190 - L grey, without terminals	326 990 01	8/1