

Product selected: FHO 39W/830

A new generation of triphosphor High Output slim linear fluorescent tubes offering superior colorimetric, photometric and lumen maintenance performance. Particularly suitable for use in the new low profile recessed and suspended luminaires and modular systems.2. FHO - Fluorescent High Output is the optimised solution for indirect lighting.

Applications

- Industrial and commercial lighting
- Shops
- Department stores
- Restaurants and reception areas

Features

- Higher lumen output: from 1850 lm to 4900 lm
- Almost constant lumen maintenance throughout the entire life of the lamp due to Luxline Plus triphosphor technology
- High colour rendering (Ra85/Class1B)
- For electronic ballast operation only giving greater efficiency and advantages in improved starting and life performance
- Optimised ambient operating temperature at 35° C (max lumen output) allows compact luminaire designs
- Reduced storage volume and transportation costs
- Average rated life: up to 20000 hours

Product Image




Line Drawing



Lamp Cap


G5



Product Attributes

Item description	FHO 39W/830
Ordering Code	0002775
EAN code	5410288027753
Packing Quantity	25
Wattage (W)	39
Voltage (V)	112
Cap	G5
Max. Over. Length (mm)	863.2
Diameter (mm)	16
Light output (lm)	3500
Bulb finish	Warmwhite Deluxe
CRI	1B

Spectral Diagram



$x = 0.440$ CRI (Ra) = 85
 $y = 0.403$ Tc = 3000K