

# 9330 MONOCHROME LASER PRINTER



**Print speeds Up to 30 ppm**

**Choice of models – simplex or duplex**

**Small and compact design**

**1200 x 1200 dpi print quality**

**8.5 seconds first time to print**

**Ideal for workgroups or small networks**

## TRANSFORM YOUR BUSINESS

### SMALL AND EFFICIENT

Ideally suitable for workgroups or small networks, the feature rich 9330 mono laser printer will transform your documents increasing overall efficiency in your office. True 1200 dpi print quality coupled with a fast 30 page per minute print speed, it delivers professional quality output all within your budget.

### CHOICE OF MODELS

The 9330N offers two input paths, a 250 sheet cassette together with a 50 sheet multi-purpose feeder ideal for those non standard paper sizes. PCL and PostScript 3 is standard together with 64 Mb of onboard memory expandable to 320 MB, will ensure the 9330N will speed through the most complex applications.

For duplex printing, the 9330ND comes complete with its own built-in duplexer for hassle-free double sided printing on a wide variety of paper types and sizes. Both models can benefit from an additional optional 250 sheet cassette which can be easily added.

### VERSATILE

USB 2.0 connectivity is standard on all models together with Ethernet 10/100BaseT and parallel, making the 9330 the most versatile printers available today. With a small footprint, it is ideally suited where space is at a premium.

# 9330 MONOCHROME LASER PRINTER

**Available Configuration**.....**9330**: Available in 2 configurations

<b>Print Speed</b> .....	30 ppm
<b>Print Method</b> .....	Laser
<b>Processor</b> .....	SPGPv3 processor at 400 MHz
<b>Resolution</b> .....	1200 x 1200 dpi
<b>Time To 1st Page</b> .....	From ready mode: < 8.5 seconds; From power save mode: 39 sec.
<b>Memory</b> .....	64MB expandable to 320MB
<b>Standard Connectivity</b> .....	Parallel (Bi-directional IEEE 1284 compliant ECP/Nibble/Byte Mode), USB (v 2.0), Internal Ethernet (10BaseT and 100BaseTx); automatic interface switching
<b>Standard Emulation</b> .....	PCL6, PCL 5e, IBM Proprinter, Epson, Postscript Level 3 PDL, automatic emulation sensing
<b>Print Monitor</b> .....	SyncThru, SET IP
<b>Fonts</b> .....	1 Bit Map and 45 scaleable (35 Intellifont, 10 TrueType), 136 PS3 fonts
<b>Consumables</b> .....	High yield cartridge: 8,000 pages; standard yield cartridge: 4,000 pages (based on 5% coverage)
<b>STD Paper Handling</b> .....	Manual feed, 50 sheet multi-purpose feeder( MPF ) plus 250 sheet universal cassette
<b>Optional Paper Handling</b> .....	2nd universal cassette accepts 250 sheets
<b>Duplexing</b> .....	Standard on 9330DN
<b>Paper Drive</b> .....	Envelope sizes: Monarch, No 9, No 10, C5, DL
<b>Paper Type</b> .....	MPF - paper, transparencies, labels, heavy paper stock, envelopes; Standard cassette - paper; Optional cassette - paper
<b>Paper Weight</b> .....	Cassette - 60 to 90 g/m <sup>2</sup> ; MPF - 60 to 163 g/m <sup>2</sup>
<b>Paper Size</b> .....	MPF - A4, A5, A6, Letter, Legal, Folio, Executive, ISO B5, JIS B5, 3" x 5"; Standard Cassette - A4, A5, Letter Legal, Folio, Executive ISO B5, JIS, 3" x 5"; Optional Cassette - A4, A5, Letter, Legal, Folio, Executive ISO B5, JIS, 3" x 5"
<b>Paper Output</b> .....	150 sheet face down, 1 sheet face up
<b>Physical Weight</b> .....	10.6 lbs. (23.3 kg)
<b>Physical Size</b> .....	15.75" x 17.1" x 11.2" (400 x 433.4 x 285 mm)
<b>Power Voltage</b> .....	120V 50/60Hz or 230V 50/60Hz
<b>Power Consumption</b> .....	Less than 11 watts in sleep mode, less than 400 watts printing; (TEC) 3.09 kWh/week
<b>Compliance</b> .....	RoHS, Microsoft, ISO-compliant, Meditech Approved, Qualified (Duplex model)
<b>Workload</b> .....	Up to 35,000 pages per month

<b>Drivers</b> .....	Windows 9.x/NT 4.0/2000/ME/Vista, MAC OSX to 10.4, DOS Print available
<b>Temperature</b> .....	Operating: 50°F to 89.6°F (10° to 32°C)
<b>Humidity</b> .....	Operating: 10% to 80% relative humidity, non-condensing
<b>Acoustic</b> .....	Printing - 54 dBA; Standby - 39 dBA
<b>Warranty</b> .....	For warranty information go to <a href="http://www.tallygenicom.com">www.tallygenicom.com</a>
<b>Option 1</b> .....	2nd cassette (250 sheet)
<b>Option 2</b> .....	16/32/64/128Mb Memory

