



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B7	Released as per ECR-08-025177	07.Oct.2008	GG	TS
	B8	REVISED PER ECR-17-014013	05JAN2018	SRG	MK0
	B9	ECR-21-123577	21MAR2022	RK	JB



NOTES

1. PACKAGING 50 PIECES IN A BOX



OBSOLETE	OBSOLETE	OBSOLETE	OBSOLETE	OBSOLETE													
1	1	1	1	1	-	-	-	-	-	Flange gasket HB.24	Neoprene	Black	9	2.0 mm Thick	108	130	140
-	1	1	1	1	-	-	-	-	-	Flange gasket HB.24	Viton compound	Black	8	3.0 mm Thick	108	130	140
-	1	1	1	1	-	-	-	-	-	Flange gasket HB.16	Viton compound	Black	7	3.0 mm Thick	81	103	113
-	1	1	1	1	-	-	-	-	-	Flange gasket HB.10	Viton compound	Black	6	3.0 mm Thick	63	83	93
-	1	1	1	1	-	-	-	-	-	Flange gasket HB.6	Viton compound	Black	5	3.0 mm Thick	50	70	80
-	1	1	1	1	1	-	-	-	-	Flange gasket HB.24	Cell India rubber“B”	Black	4	2.5 mm Thick,on one side self adhesive	108	130	140
-	1	1	1	1	-	1	-	-	-	Flange gasket HB.16	Cell India rubber“B”	Black	3	2.5 mm Thick,on one side self adhesive	81	103	113
-	1	1	1	1	-	-	1	-	-	Flange gasket HB.10	Cell India rubber“B”	Black	2	2.5 mm Thick,on one side self adhesive	63	83	93
-	1	1	1	1	-	-	-	1	-	Flange gasket HB.6	Cell India rubber“B”	Black	1	2.5 mm Thick,on one side self adhesive	50	70	80
1-3	1-2	1-1	1-1	1-0	0-9	0-4	0-3	0-2	0-1	DESCRIPTION	MATERIAL	COLOR	POS	NOTES	A	B	C
HB.24.D-2mm	HB.24.D.V	HB.16.D.V	HB.10.D.V	HB.6.D.V	HB.24.D	HB.16.D	HB.10.D	HB.6.D									

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:
n-ISO 8015
n-ISO 2768-mH-E
n-DIN 16901-120

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

1

2

DWN Schneider 11.01.1999

CHK Schweiger 11.01.1999

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

NAME
Flange mounted seal
HB 6-24
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1106352

RESTRICTED TO

CUSTOMER DRAWING

SCALE 1:2

SHEET 1 OF 1

REV B9