

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC


DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REV PER ECR 05-004247	08JUN05	JR	TM



- 1 STAMP "AMP 8*" , APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 0.00254 MIN THK TIN PER ASTM B-545
- 4 170°C MAX RECOMMENDED OPERATING TEMPERATURE.
- 5 WIRE CROSS SECTIONAL AREA RANGE:
6.64-10.5mm² (13-100-20,800) CMA
SOLID OR STRANDED

AMP
WIRE RANGE8 AWG
SOLID OR STRANDED

500	LOOSE PIECE	160013
QTY	PACKAGE TYPE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 5° FINISH
MATERIAL - 2	3

DWN	jr ruth	08JUN05
CHK	T MICHIELUTTI	08JUN05
APVD	T MICHIELUTTI	08JUN05
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING		

tyco
ElectronicsTyco Electronics Corporation
Harrisburg, Pa 17105-3608NAME
TERMINAL, RING TONGUE,
SOLISTRAND

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-160013	-
SCALE 1:1		SHEET 1 OF 1	REV B1