




NOTE:
1.MATERIAL:
HOUSING: THERMOPLASTIC WITH 30% G/F, UL 94V-0, NATURE COLOR.
CONTACTS: PHOSPHOR BRONZE.
TABS:BRASS.
2.FINISH:
CONTACT: 3.048μm (120μ") MIN. MATTE-TIN OVER
1.27μm (50μ") MIN. NICKEL ON ENTIRE CONTACT.
TABS: 3.048μm (120μ") MIN. MATTE-TIN OVER
1.27μm (50μ") MIN. NICKEL ON ENTIRE CONTACT.
3.REFLOW SOLDER CAPABLE TO 260°C PER TE CONNECTIVITY SPEC.
109-201, CONDITION B.
4.NO TE LOGO AND DATE CODE ON THE PRODUCT.
5.PART NO. OF RECEPTACLE CONTACT & HOUSING (BASE NO.#):
1734597 & 1470364.
△NO ACCUMULATE TOLERANCE.

0.21g	15.50	17.30	14.00	15	1-1734709-5
0.20g	14.50	16.30	13.00	14	1-1734709-4
0.19g	13.50	15.30	12.00	13	1-1734709-3
0.17g	12.50	14.30	11.00	12	1-1734709-2
0.16g	11.50	13.30	10.00	11	1-1734709-1
0.15g	10.50	12.30	9.00	10	1-1734709-0
0.14g	9.50	11.30	8.00	9	1734709-9
0.12g	8.50	10.30	7.00	8	1734709-8
0.11g	7.50	9.30	6.00	7	1734709-7
0.10g	6.50	8.30	5.00	6	1734709-6
0.09g	5.50	7.30	4.00	5	1734709-5
0.08g	4.50	6.30	3.00	4	1734709-4
0.07g	3.50	5.30	2.00	3	1734709-3
0.05g	2.50	4.30	1.00	2	1734709-2
WEIGHT	DIMENSIONS			NO. OF CONTACTS	PART NUMBER
	C	B	A		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
F. YANG
10APR2009

CHK
S. CHIEN
10APR2009

APVD
W. KODAMA
10APR2009

DIMENSIONS:
MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± 0.25
3 PLC ± 0.15
4 PLC ± -
ANGLES ± 5°

MATERIAL
SEE NOTE

FINISH
SEE NOTE

PRODUCT SPEC
108-57264
QUALIFICATION TEST REPORT
501-57283
WEIGHT
SEE TABLE

CUSTOMER DRAWING

NAME
TE Connectivity

WIRE TO BOARD CONNECTOR
SIDE ENTRY, SINGLE ROW, SMT TYPE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1734709

RESTRICTED TO

SCALE
-

SHEET
1 OF 3

REV
B1

