





6.8 IN EXTRACTOR: SHADOW MAX. COMPONENT HEIGHT AREA SEE RECOMMENDED PCB LAYOUT



NOTES:

1. MATERIAL:
 - 1.1 HOUSING: THERMOPLASTIC(PA66) U194V-0;
 - 1.2 EXTRUDER: COLDFUSE TABLE U194V-0;
 - 1.3 CONTACTS: COLDFUSE TABLE
 - 1.4 BOARDLOCK: BRASS
2. FINISH:
 - 2.1 CONTACT:
 - GOLD PLATING ON CONTACT AREA
 - 2.2 BOARDLOCK: TIN PLATING ON SOLDER TAIL AREA
 - 2.3 HOUSING: 500 μ MIN. NICKEL UNDERPLATING OVERALL.
 - 2.2 BOARDLOCK:
 - 500 μ MIN. NICKEL UNDERPLATING OVERALL.
 - 100 μ MIN. WARE TAIL PLATING ON SOLDER TAILS.
3. WAVE SOLDER CAPABLE TO 265C PER TYP. SPEC. 19-202, CONDITION B.



EXTRACTOR COLOR	HSC COLOR	DMA L	PART PLAYING	1775802-1									
				3.18	15u*	4-	-7	15u*	3-	-6	15u*	5-	-5
BLACK	BLACK	3.18	G/F	15u*	4-	-7	15u*	3-	-6	15u*	5-	-5	
													2.67
	DARK BLUE 28°C	3.18	G/F	15u*	9-	-3	30u*	9-	-5	15u*	9-	-5	
													2.67
	NATURE	3.18	G/F	8-	-4	30u*	8-	-6	G/F	9-	-1		
												2.67	15u*
	ORANGE 11°C	3.18	15u*	7-	-4	30u*	7-	-6	G/F	7-	-3		
												2.67	15u*
	TURPOURISE 32°C	3.18	15u*	6-	-6	30u*	6-	-6	G/F	6-	-3		
												2.67	15u*
WHITE	RED (199C)	3.18	15u*	5-	-4	30u*	5-	-5	G/F	5-	-3		
												2.67	15u*
	BLUE (2945C)	3.18	G/F	4-	-3	30u*	4-	-6	G/F	4-	-6		
												2.67	15u*
	YELLOW (115C)	3.18	15u*	3-	-4	30u*	3-	-6	G/F	3-	-3		
												2.67	15u*
	GREEN (3258C)	3.18	15u*	1-	-4	30u*	1-	-5	G/F	1-	-2		
												2.67	15u*
	BLACK	3.18	G/F	1-	-4	30u*	1-	-5	G/F	1-	-2		
												2.67	15u*
EXTRACTOR COLOR	HSC COLOR	DMA L	PART PLAYING	3.18	15u*	4-	-7	15u*	3-	-6	15u*	5-	-5

				TOLERANCES UNLESS OTHERWISE SPECIFIED		DIM	S. HOU
F	REVISED	ECR-06-010456	5H WK 2006	1 P/LC ± 0.3	2 P/LC ± 0.2	CHK	22-MAY-2006 W. J. KE
E	REVISED	ECR-05-016050	5H WK 2005	3 P/LC ±	22-MAY-2006		
D	REVISED	ECR-05-001033	5H WK 2005	ANGLES ± .3		APVD	W. J. KE 22-MAY-2006
C	ADD P/NS	F200-0293-04	5H WK 2004	08REC		PRODUCT SPEC 108-57376	
B	REVISED	F200-0268-04	5H WK 2004	32NOV		QUALIFICATION TEST REPOERT 501-57407	
A	REVISED	F200-0118-04	5H WK 2004	11JUN		WEIGHT 9.4 GRAM	
0	FIRST RELEASED	F200-0082-04	5H WK 2004	11MAY	SEE NOTE		
LTR	REVISION RECORD	ECN	DIM CHK DATE				

tyco
Electronics
TYCO HOLDINGS (BERMUDA)
VII LTD. TAIWAN BRANCH
ME
DDR1 240PIN
SOCKET CONNECTOR

△

11

○

88

7



②

(л)


(N)

2

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP (TAIWAN) LTD.
DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT.



PLUG COMPONENT:DDR II 240P FUNCTION CARD



DETAIL A
SCALE 3:1 (1.8V)

TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN	S. HOU	tyco TYCO HOLDINGS (BERMUDA) Electronics VIA LTD. TAIWAN BRANCH NAME DDRII 240PIN
0	PIC	±0.1	22-MAY-2006	
1	PIC	±0.05		
2	PIC	±0.02	W.J. KE	
3	PIC	±0.005		
ANGLES ±0.5°			22-MAY-2006	
MATERIAL		APVD	W.J. KE	

DDRII 240PIN
SOCKET CONNECTOR

SEE NOTE



PRODUCT SPEC

FINISH

QUALIFICATION TEST REPORT —

LOC	SIZE	DRAWING NO	REV
DW	A ₃	1775802	F

	SEE SHEET 1		
LTR	REVISION RECORD	ECN	DWN DATE



- NOTES :
- MATERIAL :
 - 1.1 TRAY : PVC
 - 1.2 SHIPPING CARTON : CORRUGATED FIBERBOARD
 - DIMENSION :
 - 2.1 TRAY : L=363, W=255, H=33
 - 2.1 SHIPPING CARTON : L=380, W=270, H=340
 - QUANTITY :
 - 3.1 PRIMARY PACKING: 50 PCS/TRAY
 - 3.2 SECONDARY PACKING: 10 TRAY/CARTON(500PCS)
 - WEIGHT :
 - 4.1 NET WEIGHT : 4.7kg
 - 4.2 GROSS WEIGHT : 6.95kg

LTR	SEE SHEET 1
REVISION RECORD	
EON	DWN
CHK	DATE

TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN		S. HOU	
0 P.L.C	±			22-MAY-2006	
1 P.L.C	±			W.J. KE	
2 P.L.C	±			22-MAY-2006	
3 P.L.C	±			W.J. KE	
ANGLES	±				
MATERIAL		APVD		W.J. KE	
		22-MAY-2006			
SEE NOTE		PRODUCT SPEC			
		-			
FINISH		QUALIFICATION TEST REPORT			
		-			
SEE NOTE		WEIGHT			
		-			
		LOC		SIZE	
		DW		DRAWING NO	
		A3		1775802	
		SCALE		SHEET	
		--		3 OF 3	
				REV	
				F	

tyco
Electronics
TYCO HOLDINGS (BERMUDA)
VII LTD. TAIWAN BRANCH

DDRII 240PIN
SOCKET CONNECTOR