

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD


C1

REVISED PER ECO-11-005140


01APR11


RK

HMR

INSERTO SERRACAVI
(CLAMPING INSERT)CORPO CORAZZA
(CABLE CLAMP BODY)#5-20 VITI AUTOFILETTANTI IN ACCIAIO ZINCATO (Q.TA' 2)
(#5-20 SELF-TAPPING SCREWS, ZINC PLATED STEEL, Q.TY 2)AREA SERRAGGIO CAVI
(CLAMPING AREA)

3

1) MATERIALE : TERMOPLASTICO, COLORE NERO
(MATERIAL : THERMOPLASTIC, BLACK COLOUR)2) PARTICOLARI FORNITI NON ASSEMBLATI IN SACCHETTO DI PLASTICA
(PARTS PACKAGED UNASSEMBLED INTO A PLASTIC BAG)3) L'AREA SERRAGGIO CAVI E' VARIABILE DA 6.45 A 103.9 mm²
IN FUNZIONE DEL TIPO E POSIZIONE DELL'INSERTO SERRACAVO
(CABLE CLAMPING AREA ADJUSTABLE FROM .010 TO .410 SQ. IN.
BY SELECTING AND REVERSING CLAMPING INSERTS)4) QUESTO CONNETTORE E' RICONOSCIUTO  E CERTIFICATO 
(THIS CONNECTOR IS UL RECOGNIZED AND CSA CERTIFIED)5) Ø MAX DEL FASCIO CAVI = 11.5 mm.
(MAXIMUM CABLE O.D. = .453 IN.)P/N 182655-1 COME RAPPRESENTATO
(P/N 182655-1 AS SHOWN)

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN R. FABRIS 06DEC00		CHK -		APVD C. TARTARI		NAME C.P.C. CABLE CLAMP KIT SIZE 17					
		0 PLC ± 1 PLC ± ±0.3 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±2°		PRODUCT SPEC 108-10024		APPLICATION SPEC -		SIZE A3		CAGE CODE 00779		DRAWING NO C=182655			
MATERIAL -		FINISH -		WEIGHT -		CUSTOMER DRAWING		SCALE 2:1		SHEET 1		OF 1		REV C1	



TE Connectivity