

4




3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		C	REV PER OG3A-0112-05	16FEB05	JR	TM



1 INSULATION RANGE IS .170 MAX

2 FITS TAB .032 THK

3 MATERIAL: TERMINAL - BRASS
SLEEVE: NYLON4 FINISH: TERMINAL - TIN PLATED
SLEEVE - COLOR BLUE

4000	TAPE MOUNTED	184235-2
1000	LOOSE PIECE	184235-1
QTY	SUPPLIED AS	PART NO


AMP INCORPORATED
CUSTOMER SERVICE SYSTEMSFOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY



1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.MAX RECOMMENDED OPERATING
TEMPERATURE:
[105°C] 221° FVOLTAGE RATING:
300V MAXCIRCULAR MIL AREA:
[1.04-2.62mm²] 2,050-5,180
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± .015
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISHDWN L OLMEDA 16JAN96
CHK M ELLIS 16JAN96
APVD B BARE 16JAN96
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
Harrisburg, Pa 17105-3608NAME
RECEPTACLE, 187 SERIES,
FASTON, PIDG,
WIRE SIZE: 16-14

SIZE A3 CAGE CODE 00779 DRAWING NO C-184235 RESTRICTED TO -

SCALE 6:1 SHEET 1 OF 1 REV C